



Current Ratings

70, 80, 90 and 100 Amperes

Voltage Ratings

1-pole – 277 Vac (125 Vdc)

2- and 3- pole – 480 Vac (250 Vdc)

Frequency Ratings

60 Hertz

Molded Case Circuit Breaker

Type TEY and TEYF, 70-100 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

GES6239

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.