



Products reference	DIMENSIONS							
	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	F(mm)	G(mm)	H(mm)
NF..., AF09...38(Z)-xx-xx-xx	6.5	2	45	80	44.9	32.7	10	x
NF..., AF09...38Z-xx-xx-30	6.5	2	45	80	64.9	52.7	10	x
AF40..65-30-xx-xx	10.8	0	55	119.5	40	27.8	x	10
AF40..65-40/22-xx-xx	17.8	0	70	119.5	40	27.8	x	10
AF80..96-30-xx-xx	17.8	0	70	119.5	40	27.8	x	10
AF80..96-40/22-xx-xx	28	0	90	119.5	40	27.8	x	10

Nota A: -35mmx7.5mm EN/IEC 60715 allowed for all models except AF40...65-40/22-xx-xx and AF80...96-xx-xx-xx.
 -35mmx15mm EN/IEC 60715 allowed for all models.

(1) Minimum distance to grounded component.

Code article		Material		Heat treatment		Surface treatment		Finish	
Created by	Andre Imperato	Checked by		Approved by	Hugo Guilhem-Ducleon				
Created on	2018-03-12	Checked on		Approved on	2018-05-24				
	Comments							Folio: 1/1	
	ECN number	Approuvé	Language: FR/EN	Format: A3	Scale: 1:1	PRU : FRFRA			
Title		AF09..96.. + RA4 OVERALL DIMENSIONS			PRT		1SBB505153R3501 B.3		
Title (en)		AF09..96.. + RA4 Overall Dimensions			DRW		1SBB505153D3501 B.5		