

PRODUCT SPECIFICATION

CTIND3LS5DS

Indulux Self-Contained IP68 Naveo Surface

Catalogue Number **CTIND3LS5DS**
GID **7TCA091720R0182**
Warranty **4 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **316L stainless steel/plastic**
Colour **Silver/Clear**
Dimensions (LxWxD) **398 x 100 x 100 mm**
Temperature Range **0 to 40°C**
Weight **2 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiMH**
Monitoring Equipment **Naveo®Pro**
Lamp **2 x 10W LED**
Emergency Light Output (Lumens) **400**
Average Lifespan light source (Hours) **60000 Hours**
Light Colour/Temperature/CRI **White / 6000 / 80**
Degree of Protection **IP68 IK10**

Type of Legend **Single or Double Sided**
Exit Sign Viewing/Recognition Distance (m) **17**
Nominal Voltage **220-240v AC 50Hz**
Power Consumption **15 VA / 7 Watts**
Current **Nominal: 65mA (mA)**

Accessories

102601K Cable Entry Cover kit
102702K



Configurable pictograms included



Luminaire

IoT

IK
10

IP
68

LED
●●●