



Current Ratings

15, 20, 25, 30, and 35 Amperes

Voltage Ratings (Max.)

1-pole – 277 Vac (125 Vdc)

2- and 3-pole – 480 Vac (250 Vdc)

Frequency Ratings

60 Hertz

Molded Case Circuit Breaker

Type TEYD, TEYH, TEYL, 15-35 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous

Time-current Curves

Curves show enclosure- compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

DES079

Adjustments

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.