



EVA-CIP-22 + SNOER GST 18/3 2M

Slave 2 watt, 230 Volt aluminium recess 22 meter led luminaire, series Evago the luminaire is including the pictogram PP 220/51 + GST18/3-2M connection

Product Information

| | |
|-----------------|--|
| Type | EVA-CIP-22 + SNOER GST 18/3 2M |
| Catalog number | SN4510256062-003 |
| Category_ | Escape route signalisation |
| GTIN | 08713812769929 |
| GID | 7TCA091130R0539 |
| Serie | Evago |
| Warranty (Year) | 5 |
| Other | The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard. Including round and square decorative covers. Equipped with a Wieland GST18 / 3 - 2 meter connection cable. |



Characteristics

| | |
|---------------------------------------|-------------------------------------|
| Power supply system | Central |
| Continuous operation | Yes |
| Mounting Method | Ceiling |
| Mounting form | Recess |
| Material housing | Aluminium / plastic |
| Colour housing | Aluminium |
| Material | Aluminium / polycarbonate |
| Colour | Aluminium |
| Length (mm) | 235 |
| Width (mm) | 84 |
| Height/depth (mm) | 134 |
| Maximum outer diameter (mm) | 84 |
| Built-in length (mm) | 210 |
| Built-in width (mm) | 68 |
| Built-in diameter (mm) | 68 |
| Built-in depth (mm) | 48 |
| Nominal voltage (V) | 230 |
| Voltage type | AC/DC |
| Monitoring equipment | None |
| With lamp | Yes |
| Lamp Type | Led |
| Lamp holder | Other |
| Lamp power (W) | 2 |
| Number of lamps | 1 |
| Average lifespan light source (hours) | 100.000 |
| Colour of light | White |
| Colour temperature (K) | 5000 |
| CRI | 80 |
| Protection class | II |
| Degree of protection (IP) | 40 |
| With remote switch connection | No |
| Wiring system | Maintained / non-maintained circuit |
| Type of indicator | Single / double-sided |
| Labelling type | Insert sheet/plate |

| | |
|---|---------|
| Recognition distance (m) | 22 |
| Circuit | Other |
| Power consumption maintained mode (W) | 4 |
| Apparent power consumption maintained mode (VA) | 4,4 |
| Nominal current (mA) | 19 |
| Inrush Current (A - 0.1ms) | 3 |
| Powerfactor | > 0,9 |
| Temperature range (°C) | 0 ~ +35 |

Article Details

| | |
|-----------------|---------------------|
| Product class | Emergency luminaire |
| E-code | EC001957 |
| Discount group | 30405 |
| Harmonized code | 9405408440 |
| GLN | 8713812000008 |

Ordering information

| | |
|------------------------|--------|
| Orderable | Yes |
| Order-Unit | Pieces |
| Minimum order quantity | 1 |
| Order Increment | 1 |

Supply Information

| | |
|-----------------------------------|----------------|
| Weight (kg) | 1,015 |
| Packaging | Cardboard box |
| Packaging dimensions (LxWxH) (mm) | 300 x 205 x 88 |