

TECHNICAL DATA SHEET

Type EXQ

Metric and NPT straight fitting
LT metallic range



Liquid tight conduit fitting for use with
EX LT range of metallic conduit.

Certifications / Standards:**Features & benefits:**

- Metallic fitting for use with liquid tight conduit
- Ex eb Ex tb approved
- Suitable for use in zones 1, 2, 21 and 22

Temperature range:

- EX*HC -35°C to +105°C
- EX*T -20°C to +70°C
- EX*B -20°C to +70°C
- EX*UB -20°C to +70°C

Material / Materials / Finishes:

- Nickel plated brass/stainless steel 316L
- Brass seal
- Silicone O'ring
- Nylon anti-abrasion throat

Conforms to:

- EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386 Compliant
- For use with Ex LT conduits:
- Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X
 - Ex eb IIC Gb
 - Ex tb IIIC Db

—
Product information - Metric thread

Part no.	Conduit Size		Thread Metric	Length (mm)	Across Flats (mm)
	Metric (mm)	US Trade (in.)			
EXQM0303	16	3/8	M16x1.5	21.0	25.4
EXQM0304	16	3/8	M20x1.5	21.0	25.4
EXQM0404	20	1/2	M20x1.5	22.0	28.5
EXQM0505	25	3/4	M25x1.5	25.0	35.0
EXQM0606	32	1	M32x1.5	30.0	42.0
EXQM0707	40	1-1/4	M40x1.5	38.0	52.0
EXQM0808	50	1-1/2	M50x1.5	41.0	60.0
EXQM0909	63	2	M63x1.5	46.0	70.0

*For stainless steel fittings, please add S after M in the part number, e.g. EXQMS0303

**Compatible with: EX*B, EX*T, EX*HC, EX*UB Conduits

—
Product information - NPT thread

Part no.	Conduit Size		Thread NPT	Length (mm)	Across Flats (mm)
	Metric (mm)	US Trade (in.)			
EXQA0304	16	1/2	1/2	21.0	25.4
EXQA0404	20	1/2	1/2	22.0	28.5
EXQA0505	25	3/4	3/4	25.0	35.0
EXQA0606	32	1	1	30.0	42.0
EXQA0707	40	1-1/4	1-1/4	38.0	52.0
EXQA0808	50	1-1/2	1-1/2	41.0	60.0
EXQA0909	63	2	2	46.0	70.0

*Also available in stainless steel. Please add S after A in the part number, e.g. EXQAS0304

**Compatible with: EX*B, EX*T, EX*HC, EX*UB Conduits