

PRODUCT SPECIFICATION

OW1L261HF

Aqualux 230v AC IP65 Surface

Catalogue Number **OW1L261HF**
 GID **7TCA091130R0245**
 Warranty **3 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Aluminium/Plastic**
 Colour **White/Silver**
 Dimensions (LxWxD) **381 x 170 x 75 mm**
 Temperature Range **0 to 40°C**
 Weight **1.5 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
 Battery **Mains / Central Battery**
 Monitoring Equipment **None**
 Lamp **2 x 2W LED**
 Emergency Light Output (Lumens) **89**
 Average Lifespan light source (Hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 6350 / 73**
 Degree of Protection **IP65 IK10**

Type of Legend **Single Sided (Order separate)**
 Exit Sign Viewing/Recognition Distance (m) **25**
 Nominal Voltage **220-240v AC/DC 0-60Hz**
 Power Consumption **8 VA / 3.5 Watts**
 Current **Nominal: 29.6mA (mA) Inrush: 7A**

Accessories

- XEN2W** Down ISO7010 Legend for Backlit Exit Sign
- XEN3W** Left ISO7010 Legend for Backlit Exit Sign
- XEN6W** Right ISO7010 Legend for Backlit Exit Sign
- XEN5W** Up ISO7010 Legend for Backlit Exit Sign
- XLF802W** Fire Extinguisher Legend for Backlit Exit Sign
- XLF803W** Hose Reel Legend for Backlit Exit Sign

- OW/BCM** Ceiling Bracket for Vertical Mount
- OW/BWA** Wall Bracket for Angled Mount
- OW/BWM** Cantilever Bracket for End to Wall Mount
- OW/BCR** Recessing Kit
- OW/DSC** Blank double sided diffuser for Edgelite Exit Sign

- RSEN2W** Down ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W** Left ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN6W** Right ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN5W** Up ISO7010 Legend for Edgelit Exit Sign (Single Sided)
- RSEN3W/RSEN6W** Left+Right ISO7010 Legend for Edgelit Exit Sign (Double Sided)



Edgelit Exit Sign
OW1L261HF + RSEN5W + OW/DSC



Backlit Exit Sign
OW1L261HF + XEN5W



Bulkhead
OW1L261HF

