

Product range overview

OVRH series



| Name | OVRHTP (60,120,160,200,400) | OVRHMSU | OVRHT3D | OVRHS3U | OVRHR |
|---------------------|--|-------------------|-----------------|-------------------|-----------------|
| Connection ampacity | 4000 and below | 24 A | 400 A and below | 400 A and below | 100 A and below |
| SPD type | Type 1 and Type 2 | Type 4 for Type 2 | Type 1 | Type 1 and Type 2 | Type 1 |
| Certifications | UL 1449 | UL 1449 | UL 1449 | UL 1449 | UL 1449 |
| Surge ratings | 60, 80, 100, 120, 160, 200, 240, 300, 400 kA per phase | 50 kA per phase | 50 kA per phase | 40 kA per phase | 36 kA per phase |
| LEDs | Yes | Yes | Yes | Yes | Yes |
| Dry relay contacts | Standard | Not available | Not available | Optional | Not available |
| EMI filter | Optional | Yes | Not available | Not available | Not available |
| Surge counter | Optional | Not available | Not available | Not available | Not available |
| Warranty | 10 years | 5 years | 3 years | 1 year | 1 year |