

PRODUCT SPECIFICATION

# IR2XXW3LS11

## Daylite Self-Contained Clear IP65 IR2 Surface

Catalogue Number **IR2XXW3LS11**  
GID **7TCA091170R0040**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Self-Contained (individual battery)**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Plastic**  
Colour **White**  
Dimensions (LxWxD) **342 x 98 x 72 mm**  
Temperature Range **0 to 30°C**  
Weight **0.86 Kg**

Emergency Duration (Hours) **3 Hours**  
Battery **NiCd**  
Monitoring Equipment **IR2 test**  
Lamp **1 x 2W LED**  
Emergency Light Output (Lumens) **251**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**  
Exit Sign Viewing/Recognition Distance (m) **23**  
Nominal Voltage **220-240v AC 50/60Hz**  
Power Consumption **6.1 VA / 3.9 Watts**  
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

### Accessories

- RSEN2X** Down ISO7010 Legend
- RSEN3X** Left ISO7010 Legend
- RSEN6X** Right ISO7010 Legend
- RSEN5X** Up ISO7010 Legend
- RSB1X** Arabic English Legend

**XTR** Semi-recessing bezel White



Exit Sign  
IR2XXW3LS11 + RSEN5X



Bulkhead  
IR2XXW3LS11

