

PRODUCT SPECIFICATION

# WWA8LS1

## Weatherforce 24-50v AC/DC OPAL IP65 Surface

Catalogue Number **WWA8LS1**  
GID **7TCA091130R0552**  
Warranty **3 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Mains / Slave Operation**  
Mounting Method/Form **Ceiling, Wall Surface**  
Housing Material **Metal/plastic**  
Colour **White**  
Dimensions (LxWxD) **400 x 140 x 100 mm**  
Temperature Range **0 to 40°C**  
Weight **1.52 Kg**

Emergency Duration (Hours) **Central Battery Hours**  
Battery **Central Battery**  
Monitoring Equipment **None**  
Lamp **1 x 1W LED**  
Emergency Light Output (Lumens) **207**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 4000 / 80**  
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**  
Exit Sign Viewing/Recognition Distance (m) **24**  
Nominal Voltage **24-50v AC/DC 0-60Hz**  
Power Consumption **3.4 VA / 2.1 Watts**  
Current **Nominal: 57mA (mA) Inrush: 1.1A**

### Accessories

- RSEN2120** Down ISO7010 Legend
- RSEN3120** Left ISO7010 Legend
- RSEN6120** Right ISO7010 Legend
- RSEN5120** Up ISO7010 Legend
- RSEN120** ISO7010 Legend Separate Arrow for Up, Down, Left or Right installation
- RSB1B** Arabic English Legend
- BBZ** Semi recessing bezel White



Exit Sign  
WWA8LS1 + RSEN5120



Bulkhead  
WWA8LS1

