

PRODUCT SPECIFICATION

## SR2-SWM3-G1

### Serenga 2 Self-Contained IP54 Self-Test Wall Surface

Catalogue Number **SR2-SWM3-G1**  
GID **7TCA091130R0471**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
Power Supply System **Self-Contained (individual battery)**  
Mounting Method/Form **Ceiling Surface**  
Housing Material **Aluminium/Plastic**  
Colour **White**  
Dimensions (LxWxD) **150 x 150 x 35 mm**  
Temperature Range **5 to 40°C**  
Weight **0.961 Kg**

Emergency Duration (Hours) **3 Hours**  
Battery **NiMH**  
Monitoring Equipment **Automatic self test**  
Lamp **1 x 2W LED**  
Emergency Light Output (Lumens) **203**  
Average Lifespan light source (Hours) **100000 Hours**  
Light Colour/Temperature/CRI **White / 5600 / 70**  
Degree of Protection **IP54**

Type of Legend **Not Applicable**  
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**  
Nominal Voltage **220-240v AC 50Hz**  
Power Consumption **3.5 VA / 3 Watts**  
Current **Nominal: 15mA (mA)**

### Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

