



Tolerance class according to ISO 2768-1 (Partly): Toleranseklasse i h.h.t. NS-ISO 2768-1 (Utdrag):		Tillatte avvik for basisområdet/Permissible deviations for basic range					
Medium	Rough	Betegnelse					
□	□	6	6-30	30-120	120-400	400-1000	1000-2000
□	□	± 0.1	± 0.2	± 0.3	± 0.5	± 0.8	± 1.2
□	□	± 0.2	± 0.5	± 0.8	± 1.2	± 1	± 1

For dette dokument og den her viste gjenstand forbeholder vi oss alle rettigheter. Mangfoldiggjørelse, offentliggjørelse til tredjemann eller utnyttelse av deres innhold er uten vår uttrykkelige tillatelse forbudt. ©ABB AS.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. ©ABB AS.

B	26.09.2014 AHS	Added measure front view	
A	06.03.2014 AHS	New drawing	
Prepared Utført	06.03.2014 AHS	Resp. dep. Ansv. avd.	Technology
Approved Kontroll.		Take over dep. Overtagersted	
Released Brukskl.		Revision Endring	B 29.06.2014 AHS
		Title Tittel	ZLBM123-3P Dimensional drawing
		Scale Målestokk	A3/1:5
		BOM on Drawing	
		Document No. Tegning nr.	1SEB000328
		No. o. sheets Ant. blad	1
		Sheet no. Blad nr.	1
		NORWAY	



ABB AS Division Low Voltage Products  
Skien Norway