

PRODUCT SPECIFICATION

CTOHD3LS61

Horizon Self-Contained 25M IP40 Naveo Surface

Catalogue Number **CTOHD3LS61**
GID **7TCA091180R0115**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling Surface**
Housing Material **Aluminium/Plastic**
Colour **White/Silver**
Dimensions (LxWxD) **364 x 167 x 82 mm**
Temperature Range **0 to 25°C**
Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **Naveo®Pro**
Lamp **2 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 6350 / 73**
Degree of Protection **IP40**

Type of Legend **Single or Double Sided (Order separate)**
Exit Sign Viewing/Recognition Distance (m) **25**
Nominal Voltage **220-240v AC 50Hz**
Power Consumption **9.9 VA / 5.1 Watts**
Current **Nominal: 42.5mA (mA) Inrush: 18A**

Accessories

- XEN20HS** Single Sided Down ISO7010 Legend
- XEN30HS** Single Sided Left ISO7010 Legend
- XEN60HS** Single Sided Right ISO7010 Legend
- XEN50HS** Single Sided Up ISO7010 Legend
- XB01HS** Single Sided Arabic English Legend
- XLF802HS** Fire Extinguisher Legend
- XLF803HS** Hose Reel Legend

- XEN22HD** Double Sided Down+Down ISO7010 Legend
- XEN36HD** Double Sided Left+Right ISO7010 Legend
- XEN55HD** Double Sided Up+Up ISO7010 Legend



Exit sign
CTOHD3LS61 + XEN20HS

