

PRODUCT SPECIFICATION

IND1LS5DS

Indulux 230v AC IP68 Surface

Catalogue Number **IND1LS5DS**
GID **7TCA091720R0176**
Warranty **4 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Mains / Slave Operation**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **316L stainless steel/plastic**
Colour **Silver/Clear**
Dimensions (LxWxD) **398 x 100 x 100 mm**
Temperature Range **-25 to +40°C**
Weight **1.4 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
Battery **Mains / Central Battery**
Monitoring Equipment **None**
Lamp **2 x 10W LED**
Emergency Light Output (Lumens) **800**
Average Lifespan light source (Hours) **60000 Hours**
Light Colour/Temperature/CRI **White / 6000 / 80**
Degree of Protection **IP68 IK10**

Type of Legend **Single or Double Sided**
Exit Sign Viewing/Recognition Distance (m) **17**
Nominal Voltage **220-240v AC/DC 0-60Hz**
Power Consumption **14 VA / 13 Watts**
Current **Nominal: 60mA (mA) Inrush: 2A**

Accessories

102601K Cable Entry Cover kit
102702K



Configurable pictograms included



Luminaire

