

PRODUCT SPECIFICATION

# STWWA3LS1X

## Weatherforce Self-Contained 27M IP65 Self-Test Surface

Catalogue Number **STWWA3LS1X**

GID **7TCA091160R0573**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling, Wall Surface**

Housing Material **Metal**

Colour **White**

Dimensions (LxWxD) **400 x 140 x 100 mm**

Temperature Range **0 to 30°C**

Weight **1.49 Kg**

Emergency Duration (Hours) **3 Hours**

Battery **NiCd**

Monitoring Equipment **Automatic self test**

Lamp **1 x 2W LED**

Emergency Light Output (Lumens) **207**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 4000 / 80**

Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**

Exit Sign Viewing/Recognition Distance (m) **24**

Nominal Voltage **220-240v AC 50/60Hz**

Power Consumption **6.1 VA / 3.9 Watts**

Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

### Accessories

**XEN2/2DV32** Double sided Diffuser with Down+Down ISO7010 Legend

**XEN3/6DV32** Double sided Diffuser with Left+Right ISO7010 Legend

**XEN5/5DV32** Double sided Diffuser with Up+Up ISO7010 Legend

**XB10DV32** Double sided Diffuser with Blank+Arabic English Legend

**XB11DV32** Double sided Diffuser with Arabic English+Arabic English Legend

**XB23DV32** Double sided Diffuser with Arabic English Left+Arabic English Right Legend

**XB50DV32** Double sided Diffuser with Blank+Arabic English Up Legend

**XB66DV32** Double sided Diffuser with Arabic English Down+Arabic English Down Legend

**BBZ** Semi recessing bezel White



**Double Sided Exit Sign**  
STWWA3LS1X + XEN2/2DV32

