



Rating	IEC	ANSI
Rated voltage (kV)	36	-
Phase to earth voltage (kV)	36	22
Power frequency wet (kV)	70	75
Power frequency dry (kV)	70	80
Lightning impulse (kV)	170	200
Insulation class (kV)	-	34.5
Current carrying capacity acc to IZSE2750-107		
Creepage distance 760 mm		
Mass 175 kg		
Catalogue number LF126008-B		

Prepared Sri Ambicai 2012-02-21	Responsible department PPCO/BK	Title BUSHING GOH 170-16 GENOMFÖRING GOH 170-16	Language 82
Modified by Sri Ambicai 2012-04-20	Take over department		
Approved by	Used in product	Order	Sheet no.
Revision A Mdl, Dwg updt, dim 141 w 130 & 132 w 130		Document no. 2751312-19	No. Shts. (1)



6917 028-PA(A4)Rev1

You can always look for the latest release of drawing at <http://new.abb.com/> in the selection: Products and systems - transformers- components. Or click on the link here