

CROSS REFERENCE

ReliaMod™

Modular Metering

UL Mains cross reference

Main Breaker modules: 1-Phase 3 Wire 120/240Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Main Breaker frame	kAIC	Wire entry
TMP SB4R	RMM1BL4R			XT5N	65	Top/Bottom
TMP SHB4R	RMM1BH4R	(2) 2/0 - 500	400	XT5S	100	
TMP SB6R	RMM1BL6R			XT5N	65	
TMP SHB6R	RMM1BH6R	(2) 2/0 - 500	600	XT5S	100	
TMP SB8R	RMM1BL8R			XT6N	65	
Not Offered	RMM1BH8R	(3) 2/0 - 400	800	XT6S	100	
TMP SB10R	RMM1BL10R			XT7S	65	
Not Offered	RMM1BH10R	(4) 4/0 - 500	1000	XT7H	100	
TMP SB12R	RMM1BL12R			XT7S	65	
TMP BB12RAR	RMM1BH12R	(4) 4/0 - 500	1200	XT7H	100	
Not Offered	RMM1BB14RCLL	Compression Lug Landing Pad				
TMP BB14RAR	RMM1BB14R	(4) 1/0 - 750	1400			
	RMM1BB14RL	(6) 1/0 - 750				
TMP BT14RAR	RMM1BT14R	(4) 1/0 - 750				Top
	RMM1BT14RL	(6) 1/0 - 750				
Not Offered	RMM1BB16RCLL	Compression Lug Landing Pad		T8V	100	Bottom
TMP BB16RAR	RMM1BB16R	(4) 1/0 - 750	1600			
	RMM1BB16RL	(6) 1/0 - 750				
TMP BT16RAR	RMM1BT16R	(4) 1/0 - 750				
	RMM1BT16RL	(6) 1/0 - 750				
TMP BB20RAR	RMM1BB20R					Top
TMP BT20RAR	RMM1BT20R	(6) 1/0 - 750				

Main Breaker modules: 3-Phase 4 Wire 208Y/120Vac or 120/240V Delta Hi-Leg, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Main Breaker frame	kAIC	Wire entry
TMP3SB4R	RMM3BL4R	(2) 2/0 - 500	400	XT5N	65	
TMP3SHB4R	RMM3BH4R			XT5S	100	
TMP3SB6R	RMM3BL6R	(2) 2/0 - 500	600	XT5N	65	
TMP3SHB6R	RMM3BH6R			XT5S	100	
TMP3SB8R	RMM3BL8R	(3) 2/0 - 400	800	XT6N	65	Top/Bottom
Not Offered	RMM3BH8R			XT6S	100	
TMP3SB10R	RMM3BL10R	(4) 4/0 - 500	1000	XT7S	65	
Not Offered	RMM3BH10R			XT7H	100	
TMP3SB12R	RMM3BL12R	(4) 4/0 - 500	1200	XT7S	65	
TMP3BB12RAR	RMM3BH12R			XT7H	100	
Not Offered	RMM3BB14RCLL	Compression Lug Landing Pad				
TMP3BB14RAR	RMM3BB14R	(4) 1/0 - 750	1400			Bottom
	RMM3BB14RL	(6) 1/0 - 750				
TMP3BT14RAR	RMM3BT14R	(4) 1/0 - 750				Top
	RMM3BT14RL	(6) 1/0 - 750				
TMP3BB16RCLL	RMM3BB16RCLL	Compression Lug Landing Pad				
TMP3BB16RAR	RMM3BB16R	(4) 1/0 - 750	1600	T8V	100	Bottom
	RMM3BB16RL	(6) 1/0 - 750				
TMP3BT16RAR	RMM3BT16R	(4) 1/0 - 750				Top
	RMM3BT16RL	(6) 1/0 - 750				
TMP3BB20RAR	RMM3BB20R	(6) 1/0 - 750				
TMP3BT20RAR	RMM3BT20R					Top

Main Lug modules: 1-Phase 3 Wire 120/240Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
TMPL4R	RMM1L4R	(1) 2/0-600 or (2) 2/0 - 250 or (1) 6-250	400		
TMPL6R	RMM1L6R	(2) 250-750 or (4) 3/0 - 250	600		
TMPL8R	RMM1L8R	(3) 250-750 or (6) 3/0-250	800	100	Top/Bottom
TMPL12R	RMM1L12R	(3) 250-750 or (6) 3/0-250	1200		
TMPL16R	RMM1L16R	(8) 250-750 or (16) 3/0-250	1600		
TMPL20R	RMM1L20R	(8) 250-750 or (16) 3/0 - 250	2000		

Main Lug modules: 3-Phase 4 Wire 208Y/120Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
TMP3L4R	RMM3L4R	(1) 2/0-600 or (2) 2/0 - 250 or (1) 6-250	400		
TMP3L6R	RMM3L6R	(2) 250-750 or (4) 3/0 - 250	600		
TMP3L8R	RMM3L8R	(3) 250-750 or (6) 3/0-250	800	100	Top/Bottom
TMP3L12R	RMM3L12R	(3) 250-750 or (6) 3/0-250	1200		
TMP3L16R	RMM3L16R	(8) 250-750 or (16) 3/0-250	1600		
TMP3L20R	RMM3L20R	(8) 250-750 or (16) 3/0 - 250	2000		

Main Lug modules with feed through: 1-Phase 3 Wire 120/240Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Outgoing Load Lugs per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
Not Offered	RMM1L12RFTL	(5) 250-750 or (10) 3/0 - 250	(5) 250-750 or (10) 3/0 - 250	1200		
Not Offered	RMM1L16RFTL	(8) 250-750 or (16) 3/0 - 250	(8) 250-750 or (16) 3/0 - 250	1600	100	Top/Bottom
TMPL20RCRIS	RMM1L20RFTL	(8) 250-750 or (16) 3/0 - 250	(8) 250-750 or (16) 3/0 - 250	2000		

Main Lug modules with feed through: 3-Phase 4 Wire 208Y/120Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Outgoing Load Lugs per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
TMP3L12RCRIS	RMM3L12RFTL	(5) 250-750 or (10) 3/0 - 250	(5) 250-750 or (10) 3/0 - 250	1200		
TMP3L16RCRIS	RMM3L16RFTL	(8) 250-750 or (16) 3/0 - 250	(8) 250-750 or (16) 3/0 - 250	1600	100	Top/Bottom
TMP3L20RCRIS	RMM3L20RFTL	(8) 250-750 or (16) 3/0 - 250	(8) 250-750 or (16) 3/0 - 250	2000		

Main Fusible Switch: 1-Phase 3 Wire 120/240Vac, Lugs included, Fuses not included, order separately.

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Fuse class	kAIC	Wire entry
TMPFB4R or TMPFT4R	RMM1F4R	(2) 2/0 - 500	400			
TMPFB6R or TMPFT6R	RMM1F6R	(3) 2/0 - 400	600	Class T Only	100	Top/Bottom
TMPFB8R or TMPFT8R	RMM1F8R	(4) 4/0 - 500	800			

Main Fusible Switch: 3-Phase 4 Wire 208Y/120Vac Lugs included, Fuses not included, order separately

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Fuse class	kAIC	Wire entry
TMP3FB4R or TMP3FT4R	RMM3F4R	(2) 2/0 - 500	400			
TMP3FB6R or TMP3FT6R	RMM3F6R	(3) 2/0 - 400	600	Class T Only	100	Top/Bottom
TMP3FB8R or TMP3FT8R	RMM3F8R	(4) 4/0 - 500	800			

Main Pull Box module: 1-Phase 3 Wire 120/240Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Line Lugs per Phase & Neutral (AWG/kcmil Cu/Al)	Outgoing Load Lugs per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
TMPU4R	RMM1P4R		(1) 2/0-600 or (2) 2/0 - 250 or (1) 6-250	400		
TMPU8R	RMM1P8R	Compression Lug Landing Pad	(3) 250-750 or (6) 3/0-250	600	100	Top/Bottom
TMPU12R	RMM1P12R		(3) 250-750 or (6) 3/0-250	1200		

Main Pull Box module: 3-Phase 4 Wire 208Y/120Vac, Lugs included

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Outgoing Load Lugs per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	kAIC	Wire entry
TMP3U4R	RMM3P4R		(1) 2/0-600 or (2) 2/0-250 or (1) 6-250	400		
TMP3U8R	RMM3P8R	Compression Lug Landing Pad	(3) 250-750 or (6) 3/0-250	800	100	Top/Bottom
TMP3U12R	RMM3P12R		(3) 250-750 or (6) 3/0-250	1200		

Euserc Main Breaker: w/ Pull Box, 1-Phase 3 Wire 120/240Vac

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Main Breaker frame	kAIC	Wire entry
TMPBU4R	RMM1BEL4R	Compression Lug Landing Pad	400	XT5N	65	
Not Offered	RMM1BEH4R			XT5S	100	
TMPBU6R	RMM1BEL6R	Compression Lug Landing Pad	600	XT5N	65	
Not Offered	RMM1BEH6R			XT5S	100	
TMPBU8R	RMM1BEL8R	Compression Lug Landing Pad	800	XT6N	65	
Not Offered	RMM1BEH8R			XT6S	100	Bottom
TMPBU10R	RMM1BEL10R	Compression Lug Landing Pad	1000	XT7S	65	
Not Offered	RMM1BEH10R			XT7H	100	
TMPBU12R	RMM1BEL12R	Compression Lug Landing Pad	1200	XT7S	65	
Not Offered	RMM1BEH12R			XT7H	100	

Euserc Main Breaker: w/ Pull Box, 3-Phase 4 Wire

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Main Breaker frame	kAIC	Wire entry
TMP3BU4R	RMM3BEL4R	Compression Lug Landing Pad	400	XT5N	65	
Not Offered	RMM3BEH4R			XT5S	100	
TMP3BU6R	RMM3BEL6R	Compression Lug Landing Pad	600	XT5N	65	
Not Offered	RMM3BEH6R			XT5S	100	
TMP3BU8R	RMM3BEL8R	Compression Lug Landing Pad	800	XT6N	65	
Not Offered	RMM3BEH8R			XT6S	100	Bottom
TMP3BU10R	RMM3BEL10R	Compression Lug Landing Pad	1000	XT7S	65	
Not Offered	RMM3BEH10R			XT7H	100	
TMP3BU12R	RMM3BEL12R	Compression Lug Landing Pad	1200	XT7S	65	
Not Offered	RMM3BEH12R			XT7H	100	

Euserc Main Fusible Switch w/ Pull Box: 1-Phase 3 Wire 120/240Vac

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Fuse class	kAIC	Wire entry
TMPFB4RCLL	RMM1FE4RCLL		400			
TMPFB6RCLL	RMM1FE6RCLL	Compression Lug Landing Pad	600	Class T Only	100	Bottom
TMPFB8RCLL	RMM1FE8RCLL		800			

Euserc Main Fusible Switch w/ Pull Box: 3-Phase 4 Wire, 208Y120Vac

Legacy GE Product number	Closest equivalent ABB Product number	Incoming Lug sizes per Phase & Neutral (AWG/kcmil Cu/Al)	Main Ampere rating	Fuse class	kAIC	Wire entry
TMP3FB4RCLL	RMM3FE4RCLL	Compression Lug Landing Pad	400	Class T Only	100	Bottom
TMP3FB6RCLL	RMM3FE6RCLL		600			
TMP3FB8RCLL	RMM3FE8RCLL		800			

US residential Meter Stacks cross reference

Residential Meter Stacks: 125A Socket, Ringless Type, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR8212R	RMS28212LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	4	Yes
	RMS28212HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS18212LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18212HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR8312R	RMS28312LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase In	125	3	
	RMS28312HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS18312LRLR	Only accepts THQL/THHQL tenant breakers	10,22					
	RMS18312HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR8412R	RMS28412LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase In	125	4	Yes
	RMS28412HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS18412LRLR	Only accepts THQL/THHQL tenant breakers	10,22					
	RMS18412HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR8512R	RMS28512LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase In	125	5	
	RMS28512HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS18512LRLR	Only accepts THQL/THHQL tenant breakers	10,22					
	RMS18512HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR8612R	RMS28612LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase In	125	6	
	RMS28612HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS18612LRLR	Only accepts THQL/THHQL tenant breakers	10,22					
	RMS18612HRLR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ringless Type, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR8220R	RMS28222LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			2	
	RMS28222HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18222LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In				
	RMS18222HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR8320R	RMS28322LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			3	
	RMS28322HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18322LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In				
	RMS18322HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100	1-Phase Out				
TMPR8420R	RMS28422LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			4	Yes
	RMS28422HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18422LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In				
	RMS18422HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR8520R	RMS28522LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			5	
	RMS28522HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18522LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In				
	RMS18522HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

Residential Meter Stacks: 125A Socket, Ringless Type, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR8212RHB	RMS28212LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			2	
	RMS28212HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS18212LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18212HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR8312RHB	RMS28312LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			3	
	RMS28312HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS18312LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18312HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR8412RHB	RMS28412LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			4	Yes
	RMS28412HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS18412LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18412HHBR	Only accepts TEY tenant breakers	42,65,100	1-Phase Out				
TMPR8512RHB	RMS28512LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			5	
	RMS28512HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS18512LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18512HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR8612RHB	RMS28612LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			6	
	RMS28612HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS18612LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In				
	RMS18612HHBR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ringless Type with Horn Bypass, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR8220RHB	RMS28222LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	2	Yes
	RMS28222HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18222LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			2	
	RMS18222HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR8320RHB	RMS28322LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	3	Yes
	RMS28322HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18322LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			3	
	RMS18322HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR8420RHB	RMS28422LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	4	Yes
	RMS28422HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18422LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			4	
	RMS18422HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR8520RHB	RMS28522LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	5	Yes
	RMS28522HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18522LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			5	
	RMS18522HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

Residential Meter Stacks: 125A Socket, Ring Type, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMP8212R	RMS28212LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	2	No
	RMS28212HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS18212LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			2	
	RMS18212HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP8312R	RMS28312LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	3	No
	RMS28312HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS18312LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			3	
	RMS18312HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP8412R	RMS28412LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	4	No
	RMS28412HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS18412LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			4	
	RMS18412HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP8512R	RMS28512LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	5	No
	RMS28512HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS18512LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			5	
	RMS18512HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP8612R	RMS28612LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	6	No
	RMS28612HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS18612LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			6	
	RMS18612HRGR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ring Type, with 800A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMP8220R	RMS28222LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	2	No
	RMS28222HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18222LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			2	
	RMS18222HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP8320R	RMS28322LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	3	No
	RMS28322HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18322LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			3	
	RMS18322HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP8420R	RMS28422LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	4	No
	RMS28422HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18422LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			4	
	RMS18422HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP8520R	RMS28522LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	5	No
	RMS28522HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS18522LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			5	
	RMS18522HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

Residential Meter Stacks: 125A Socket, Ringless Type with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR12212R	RMS212212LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	2	Yes
	RMS212212HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS112212LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			2	
	RMS112212HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR12312R	RMS212312LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	3	Yes
	RMS212312HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS112312LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			3	
	RMS112312HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR12412R	RMS212412LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	4	Yes
	RMS212412HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS112412LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			4	
	RMS112412HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR12512R	RMS212512LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	5	Yes
	RMS212512HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS112512LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			5	
	RMS112512HRLR	Only accepts TEY tenant breakers	42,65,100					
TMPR12612R	RMS212612LRLR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	6	Yes
	RMS212612HRLR	Only accepts TEY tenant breakers	42,65,100					
	RMS112612LRLR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			6	
	RMS112612HRLR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ringless Type with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR12220R	RMS212222LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			2	
	RMS212222HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112222LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			2	
	RMS112222HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12320R	RMS212322LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	3	Yes
	RMS212322HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112322LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			3	
	RMS112322HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12420R	RMS212422LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			4	
	RMS212422HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112422LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			4	
	RMS112422HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12520R	RMS212522LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In			5	
	RMS212522HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112522LRLR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			5	
	RMS112522HRLR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

Residential Meter Stacks: 125A Socket, Ringless Type with Horn Bypass, with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR12212RHB	RMS212212LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			2	
	RMS212212HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS112212LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			2	
	RMS112212HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR12312RHB	RMS212312LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	3	Yes
	RMS212312HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS112312LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			3	
	RMS112312HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR12412RHB	RMS212412LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			4	
	RMS212412HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS112412LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			4	
	RMS112412HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR12512RHB	RMS212512LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			5	
	RMS212512HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS112512LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			5	
	RMS112512HHBR	Only accepts TEY tenant breakers	42,65,100					
TMPR12612RHB	RMS212612LHBR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In			6	
	RMS212612HHBR	Only accepts TEY tenant breakers	42,65,100					
	RMS112612LHBR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			6	
	RMS112612HHBR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ringless Type with Horn Bypass, with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMPR12220RHB	RMS212222LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	2	
	RMS212222HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112222LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			2	
	RMS112222HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12320RHB	RMS212322LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	3	
	RMS212322HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112322LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			3	
	RMS112322HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12420RHB	RMS212422LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	4	Yes
	RMS212422HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112422LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In	4			
	RMS112422HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMPR12520RHB	RMS212522LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	5	
	RMS212522HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112522LHBR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			5	
	RMS112522HHBR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

Residential Meter Stacks: 125A Socket, Ring Type, with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMP12212R	RMS212212LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	2	
	RMS212212HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS112212LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			2	
	RMS112212HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP12312R	RMS212312LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	3	
	RMS212312HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS112312LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			3	
	RMS112312HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP12412R	RMS212412LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In	1-Phase Out	125	4	No
	RMS212412HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS112412LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In	4			
	RMS112412HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP12512R	RMS212512LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	5	
	RMS212512HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS112512LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			5	
	RMS112512HRGR	Only accepts TEY tenant breakers	42,65,100					
TMP12612R	RMS212612LRGR	Only accepts THQL/THHQL tenant breakers	10,22	3-Phase In		125	6	
	RMS212612HRGR	Only accepts TEY tenant breakers	42,65,100					
	RMS112612LRGR	Only accepts THQL/THHQL tenant breakers	10,22	1-Phase In			6	
	RMS112612HRGR	Only accepts TEY tenant breakers	42,65,100					

Residential Meter Stacks: 225A Socket, Ring Type, with 1200A Crossbus

Legacy GE Product number	Closest equivalent ABB Product number	Special features	kAIC	Phase Input	Phase Output	Socket Amps	No. of sockets	5th Jaw included
TMP12220R	RMS212222LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In		225	2	No
	RMS212222HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112222LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			2	
	RMS112222HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP12320R	RMS212322LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	3	No
	RMS212322HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112322LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			3	
	RMS112322HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP12420R	RMS212422LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	4	No
	RMS212422HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112422LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			4	
	RMS112422HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
TMP12520R	RMS212522LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	3-Phase In	1-Phase Out	225	5	No
	RMS212522HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					
	RMS112522LRGR	Only accepts Formula A1 or A2 tenant breakers	10,22	1-Phase In			5	
	RMS112522HRGR	Only accepts XT3 or XT4 tenant breakers	42,65,100					

US commercial Meter Stacks cross reference

Meter Stacks: 225A Commercial Ringless Type Sockets with Lever Bypass

Legacy GE Product number	Closest equivalent ABB Product number	Special features	Socket Amps	No. of sockets	Phase Input	Phase Output	5th Jaw included
TMPR12122R	RMS112122CHLBR	Only accepts XT3 or XT4 tenant mains	225	1	1-Phase In	1-Phase Out	Yes
	RMS212122CHLBR				3-Phase In	1-Phase Out	
TMPR312122R	RMS312122CHLBR			3-Phase In	3-Phase Out		
TMPR12222R	RMS112222CHLBR			2	1-Phase In	1-Phase Out	
	RMS212222CHLBR				3-Phase In	1-Phase Out	
TMPR312222R	RMS312222CHLBR			3-Phase In	3-Phase Out		
TMPR12322R	RMS112322CHLBR			3	1-Phase In	1-Phase Out	
	RMS212322CHLBR				3-Phase In	1-Phase Out	
TMPR312322R	RMS312322CHLBR			3-Phase In	3-Phase Out		
TMPR12422R	RMS112422CHLBR			4	1-Phase In	1-Phase Out	
	RMS212422CHLBR	3-Phase In	1-Phase Out				
TMPR312422R	RMS312422CHLBR	3-Phase In	3-Phase Out				

Meter Stacks: 400A Commercial Ringless Type Sockets with Lever Bypass

Legacy GE Product number	Closest equivalent ABB Product number	Special features	Socket Amps	No. of sockets	Phase Input	Phase Output	5th or 7th Jaw included
TMPR12140RB	RMS112140CHLBRB	(1) 400A 65KAIC XT5N Breaker Factory Installed	400	1	1-Phase In	1-Phase Out	5th jaw included on all 1-Phase output models and 7th jaw included on all 3-phase output models
	RMS212140CHLBRB				3-Phase In	1-Phase Out	
TMPR312140RB	RMS312140CHLBRB				3-Phase In	3-Phase Out	
TMPR12240RB	RMS112240CHLBRB	(2) 400A 65KAIC XT5N Breakers Factory Installed	2	2	1-Phase In	1-Phase Out	
	RMS212240CHLBRB				3-Phase In	1-Phase Out	
TMPR312240RB	RMS312240CHLBRB	3-Phase In	3-Phase Out				
TMPR312140TR	RMS312140CHLBR	No Breakers Included, requires 2 XT3 or XT4 tenant breakers field installed, 400A max sum of both breakers, metered by one 400A socket	400	1	3-Phase In	3-Phase Out	

US Mini Mod III cross reference

Mini Mod III does not have a direct replacement. Contact your ABB representative for alternative solutions and configurations.

Mini Mod III: 1-Phase 3 Wire 120/240Vac, Ringless Type Sockets, Lugs included

Legacy GE product number	Main Ampere rating	Socket Amps	No. of sockets	kAIC
TMMR2212R	200A		2	10,22
				50,65
TMMR4312R	400A		3	10,22
				50,65
TMMR4412R	400A	125	4	10,22
				50,65
TMMR6512R	600A		5	10,22
				50,65
TMMR6612R	600A		6	10,22
				50,65
TMMR4220R	400A		2	10-100
TMMR6320R				10-100
TMMR6420R	600A	225	4	10-100
TMMR6520R				10-100
TMMR6620R	600A		6	10-100
				10-100

Mini Mod III: 1-Phase 3 Wire 120/240Vac, Ringless Type Sockets, Lugs included (with Horn Bypass)

Legacy GE product number	Main Ampere rating	Socket Amps	No. of sockets	kAIC
TMMR2212RHB	200A		2	10,22
				42,65
TMMR4312RHB	400A		3	10,22
				42,65
TMMR4412RHB	400A	125	4	10,22
				42,65
TMMR6512RHB	600A		5	10,22
				42,65
TMMR6612RHB	600A		6	10,22
				42,65
TMMR4220RHB	400A		2	10-100
TMMR6320RHB				10-100
TMMR6420RHB	600A	225	4	10-100
TMMR6520RHB				10-100
TMMR6620RHB	600A		6	10-100
				10-100

Mini Mod III: 1-Phase 3 Wire 120/240Vac, Ring Type Sockets, Lugs included

Legacy GE product number	Main Ampere rating	Socket Amps	No. of sockets	kAIC
TMM2212R	200A		2	10,22 42,65
TMM4312R			3	10,22 42,65
TMM4412R	400A	125	4	10,22 42,65
TMM6512R			5	10,22 42,65
TMM6612R	600A		6	10,22 42,65
TMM4220R	400A		2	10-100
TMM6320R			3	10-100
TMM6420R		225	4	10-100
TMM6520R	600A		5	10-100
TMM6620R			6	10-100

ABB Inc.
305 Gregson Drive
Cary, NC 27511
United States

electrification.us.abb.com

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2023 ABB
All rights reserved