

BUYLOG SECTION 3

RV power pedestals and inlets



Section Updated 11/2022

Table of contents

Overview	3-4
Ordering tables	3-5
Accessories	3-6

Ordering tables



Unmetered surface mount

Unmetered surface mount

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table ¹	Ordering code
100	120/240	30A/20A GFCI	THQL1130, THQL1120	N/A	Single Side	No	1	GE1LU032SS
70	120/240	50A/20A GFCI	THQL2150, THQL1120	N/A	Single Side	No	2	GE1LU502SS
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	3	GE1LU532SS

Ring type metered surface mount

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table ¹	Ordering code
100	120/240	30A/20A GFCI	THQL1130, THQL1120	N/A	Single Side	No	2	GE1LM032SS
70	120/240	50A/20A GFCI	THQL2150, THQL1120	N/A	Single Side	No	2	GE1LM502SS
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	4	GE1LM532SS



Ring type metered pad mount post

Unmetered pad mount post

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table ¹	Ordering code
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Back-to-Back	No	5	GE1LU532PB
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	6	GE1LU532PS
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	Yes	6	GE1LU532PSL

Ring type metered pad mount post

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table ¹	Ordering code
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	7	GE1LM532PS

Unmetered earth burial post

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table ¹	Ordering code
70	120/240	30A/20A GFCI	THQL1130, THQL1120	N/A	Single Side	No	6	GE1LU032ES
70	120/240	30A/20A GFCI	THQL1130, THQL1120	N/A	Single Side	Yes	6	GE1LU032ESL
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Back-to-Back	No	5	GE1LU532EB
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	6	GE1LU532ES
100	120/240	50A/30A/20A	THQL2150, THQL1130, THQL1120GFT	20A	Single Side	No	6	GE1LU532ESG
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	Yes	6	GE1LU532ESL

Ring type metered earth burial post

Amps	Volts	Receptacles	Circuit protection	Ground fault circuit breaker	Head type	Lighted	Wire range table	Ordering code
100	120/240	30A/20A GFCI	THQL1130, THQL1120	N/A	Single Side	No	7	GE1LM032ES
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Back-to-Back	No	8	GE1LM532EB
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	No	7	GE1LM532ES
100	120/240	50A/30A/20A	THQL2150, THQL1130, THQL1120GFT	20A	Single Side	No	7	GE1LM532ESG
100	120/240	50A/30A/20A GFCI	THQL2150, THQL1130, THQL1120	N/A	Single Side	Yes	7	GE1LM532ESL

Accessories



GEFBEM9



GESFEM9



GEUH90G



GEUWATER34

Description	Dimensions	Ordering code
Earth Burial Stabilizer Base (wire from back only)	9 in.	GEFBEM9
9" Stabilizer Foot Kit (wire from side or back)	9 in.	GESFEM9
Bolt-on TV//Telephone Kit – 5"x18" RJ11 Phone Jack, Padmount or Earth Burial	-	GETTV100
Add-on Water Shroud – Adapts to 9" wide galvanized steel post, grey color	15 1/4 in (H) x 9 1/2 in. (W)	GEUH90G
3/4" Hose Bib Faucet for Post Applications	3 1/2 in (H) x 2 in. (W)	GEUWATER34