

PRODUCT SPECIFICATION

OZ3L261

Horizon Self-Contained 25M IP20 Self-Test Wall Recess

Catalogue Number **OZ3L261**
GID **7TCA091070R0096**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Aluminium/Plastic**
Colour **White/Silver**
Dimensions (LxWxD) **364 x 167 x 82 mm**
Temperature Range **0 to 25°C**
Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **Automatic self test**
Lamp **2 x 2W LED**
Emergency Light Output (Lumens) **Not Applicable**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 6350 / 73**
Degree of Protection **IP40**

Type of Legend **Single Sided (Order separate)**
Exit Sign Viewing/Recognition Distance (m) **25**
Nominal Voltage **220-240v AC 50Hz**
Power Consumption **9.9 VA / 5.1 Watts**
Current **Nominal: 42.5mA (mA) Inrush: 18A**

Accessories

- XEN2H** Single Sided Down ISO7010 Legend
- XEN3H** Single Sided Left ISO7010 Legend
- XEN6H** Single Sided Right ISO7010 Legend
- XEN5H** Single Sided Up ISO7010 Legend
- XB01H** Single Sided Arabic English Legend
- XLF-SN802** Fire Extinguisher Legend
- XLF-SN803** Hose Reel Legend

- OH/BCM** Ceiling Bracket for Vertical Mount
- OH/WG** Protective Wire Guard



Exit Sign
OZ3L261 + XEN2H

