



RLN-3/ZT/LED

Self-contained 3 hours 1 watt, maintained surface mount/recess led renovation module, including automatic self test, series Optilux

Product Information

Type	RLN-3/ZT/LED
Catalog number	11122091-001
Category_	Escape route signalisation
GTIN	08713812746999
GID	7TCA091160R0014
Serie	Optilux
Warranty (Year)	5
Other	This replacemend / renovation LED kit is placed in the existing first fix of the original luminaire. The Optilux led is only suited for use as a escape route signalisation luminaire!



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Renovation
Mounting form	Renovation
Material housing	Plastic
Colour housing	White / aluminium
Material cover	Plastic, transparent
Material	Polycarbonate
Colour	White / aluminium
Length (mm)	364
Width (mm)	167
Height/depth (mm)	78
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	3
Battery	NiCd
Monitoring equipment	Automatic self test
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	1
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	73
Protection class	I
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Foil / acrylic plate
Recognition distance (m)	25
Circuit	Other
Power consumption maintained mode (W)	5,1

Apparent power consumption maintained mode (VA)	9,9
Nominal current (mA)	42,5
Powerfactor	0,52
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30901
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	1,087
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111