



## EVA-COP-32/ZWART

Slave 4 watt, 230 Volt black aluminium surface 32 meter led luminaire, series Evago.  
The luminaire is including the pictogram PP 320/51 (escape route straight forward) + green pictogram (PP 320/50)

### Product Information

Type	EVA-COP-32/ZWART
Catalog number	4530256053
Category_	Escape route signalisation
GTIN	08713812767789
GID	7TCA091130R0522
Serie	Evago
Warranty (Year)	5
Other	The luminaire is equipped with a light dimming circuit, the minimum output is in accordance with the standard



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Surface
Material housing	Aluminium
Colour housing	Black
Material	Aluminium
Colour	Black
Length (mm)	335
Width (mm)	66
Height/depth (mm)	222
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	4
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5000
CRI	80
Protection class	II
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	32
Circuit	Other
Power consumption maintained mode (W)	6,5
Apparent power consumption maintained mode (VA)	7,1
Nominal current (mA)	31
Inrush Current (A - 0.1ms)	3

Powerfactor	> 0,9
Temperature range (°C)	0 ~ +35

**Article Details**

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

**Ordering information**

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

**Supply Information**

Weight (kg)	1,392
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	400 x 250 x 88