



RQL 02/HF/LED/FLX

Slave 1 watt, 230 Volt surface mount led renovation module, including control module, series Aqualux

Product Information

Type	RQL 02/HF/LED/FLX
Catalog number	6000054-005
Category_	Escape route lighting;Escape route signalisation
GTIN	08713812759340
GID	7TCA091140R0285
Serie	Aqualux
Warranty (Year)	5
Other	This replacement / renovation kit is placed in the existing first fix of the original luminaire.



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Renovation
Mounting form	Renovation
Material housing	Plastic
Colour housing	White
Material cover	Plastic, transparent
Material	Polycarbonate
Colour	White
Length (mm)	350
Width (mm)	125
Height/depth (mm)	65
Nominal voltage (V)	230
Voltage type	DC
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	1
Number of lamps	2
Light output in emergency operation (lm)	89
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	73
Protection class	II
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	25
Circuit	Other
Nominal current (mA)	29,6
Temperature range (°C)	0 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30406
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,918
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	426 x 188 x 111