

PRODUCT SPECIFICATION

IR2OZD3LS61

Horizon Self-Contained 25M IP20 IR2 Recess

Catalogue Number **IR2OZD3LS61**

GID **7TCA091170R0010**

Warranty **3 Year/s Refer to ABB warranty terms & conditions**

Power Supply System **Self-Contained (individual battery)**

Mounting Method/Form **Ceiling Surface**

Housing Material **Aluminium/Plastic**

Colour **White/Silver**

Dimensions (LxWxD) **364 x 167 x 82 mm**

Temperature Range **0 to 25°C**

Weight **1.3 Kg**

Emergency Duration (Hours) **3 Hours**

Battery **NiCd**

Monitoring Equipment **IR2 test**

Lamp **2 x 2W LED**

Emergency Light Output (Lumens) **Not Applicable**

Average Lifespan light source (Hours) **100000 Hours**

Light Colour/Temperature/CRI **White / 6350 / 73**

Degree of Protection **IP40**

Type of Legend **Single or Double Sided (Order separate)**

Exit Sign Viewing/Recognition Distance (m) **25**

Nominal Voltage **220-240v AC 50Hz**

Power Consumption **9.9 VA / 5.1 Watts**

Current **Nominal: 42.5mA (mA) Inrush: 18A**

Accessories

XEN20HS Single Sided Down ISO7010 Legend

XEN30HS Single Sided Left ISO7010 Legend

XEN60HS Single Sided Right ISO7010 Legend

XEN50HS Single Sided Up ISO7010 Legend

XB01HS Single Sided Arabic English Legend

XLF802HS Fire Extinguisher Legend

XLF803HS Hose Reel Legend

XEN22HD Double Sided Down+Down ISO7010 Legend

XEN36HD Double Sided Left+Right ISO7010 Legend

XEN55HD Double Sided Up+Up ISO7010 Legend



Exit sign
IR2OZD3LS61 + XEN20HS

