



# 中国国家强制性产品认证证书

证书编号：2024010305658959

认证委托人名称及地址

ABB AG

Kallstadter Str. 1 68309 Mannheim Germany

生产者名称及地址

ABB AG - STOTZ-KONTAKT

Eppelheimer Str. 82 DE-69123 Heidelberg

生产企业名称及地址

ABB AG - STOTZ-KONTAKT

Eppelheimer Str. 82 DE-69123 Heidelberg

产品名称和系列、型号、规格

辅助触头

CA6, CAF6 Ui: 690V;Uimp: 6kV;lth: 6A;AC-15: Ue/Ie: AC240V/4A, AC440V/3A, AC500V/2A;DC-13: Ue/Ie: DC24V/2.5A, DC125V/0.7A, DC250V/0.4A;IP20; 注: DC24V 不在 CCC 认证范围内; 型号解释见附页

产品标准和技术要求

GB/T 14048.5-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》(CNCA-C03-02:2024)的要求,特发此证。

发证日期: 2026年05月15日 有效期至: 2029年07月16日

本证书为变更证书,证书首次颁发日期: 2024年07月17日  
证书信息和有效性可扫描下方二维码或登录发证机构网站查验,  
也可在认监委网站 ([www.cnca.gov.cn](http://www.cnca.gov.cn)) 查询。



签发:

刘江



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





# 中国国家强制性产品认证证书

证书编号: 2024010305658959

证书附页: 第 1 页 共 1 页

型号的解释:

$\frac{CA6}{1} - \frac{11}{2} \frac{K}{3} - \frac{P}{4}$

1: 产品型号 (product type):

CA6: 侧装, (side mounted)

CAF6: 前装 (front mounted)

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量 (contact configuration)

CA6: 11: 1NO+1NC

CAF6: 11: 1NO+1NC      20: 2NO      02: 2NC

3: 接线端子标识代号: 接触器或继电器配合代号 (suitability for)

K: K6..KC6

E: B(C)6-40-00, B(C)7-40-00

M: B(C)6-30-10, B(C)7-30-10

N: B(C)6-30-01, B(C)7-30-01

4: 接线端子类型 (terminal type):

空白 (blank): 螺钉端子 (screw)

P: 焊接插针端子 (pin)

F: 插片端子 (flat pin)

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2024010305658959

**NAME AND ADDRESS OF THE APPLICANT**

ABB AG  
Kallstadter Str. 1 68309 Mannheim Germany

**NAME AND ADDRESS OF THE MANUFACTURER**

ABB AG – STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

**NAME AND LOCATION OF THE FACTORY**

ABB AG – STOTZ-KONTAKT  
Eppelheimer Str. 82 DE-69123 Heidelberg

**PRODUCT NAME,MODEL AND SPECIFICATION**

Auxiliary Contact  
CA6, CAF6 Ui: 690V;Uimp: 6kV;lth: 6A;AC-15: Ue/Ie: AC240V/4A, AC440V/3A,  
AC500V/2A;DC-13: Ue/Ie: DC24V/2.5A, DC125V/0.7A, DC250V/0.4A;IP20; Note: DC24V is not  
covered by CCC

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of  
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** May.15,2026

**Valid until:** Jul.16,2029

Date of original issued: Jul.17,2024

The certificate information and validity could be checked by scanning the QR code below or logging in to  
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010305658959

Appendix: Page 1 of 1

CA6 - 11 K - P  
1 2 3 4

1: 产品型号 (product type):

CA6: 侧装, (side mounted)

CAF6: 前装 (front mounted)

2: 触点类型: 第一位常开触点数量, 第二位常闭触点数量 (contact configuration)

CA6: 11: 1NO+1NC

CAF6: 11: 1NO+1NC      20: 2NO      02: 2NC

3: 接线端子标识代号: 接触器或继电器配合代号 (suitability for)

K: K6..KC6

E: B(C)6-40-00, B(C)7-40-00

M: B(C)6-30-10, B(C)7-30-10

N: B(C)6-30-01, B(C)7-30-01

4: 接线端子类型 (terminal type):

空白 (blank): 螺钉端子 (screw)

P: 焊接插针端子 (pin)

F: 插片端子 (flat pin)

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.