



DOCUMENT ID. 9AKK108468A0189 REV.A APRIL 6, 2023

S300P Miniature Circuit Breakers

Product family overview

S300P Miniature Circuit Breakers

Product family overview



Technical criteria

Product name	ST200M	S200MR	S200MUC	S800S	S800C	S300P
Interrupt Rating	10/5 kA	10kA	up to 10kA	upto 30kA	upto 20kA	10kA
Current Rating	0.5 to 63A	0.2 to 63A	0.2 to 63A	0.5 to 63A	10 to 100A	0.2 to 63A
Rated Voltage	480Y/277 V AC 60/125 V DC (1-/2-pole)	480Y/277 V AC	480Y/277 V AC 250/500 V DC (1-/2-pole)	630Y/347 V AC	480Y/277 V AC upto 500 V DC	480Y/277 V AC 60/125 V DC (1-/2-pole)
Characteristics	B,C,D,K,Z	K	C,K,Z	B,C,D,K	B,C,D,K	B, C, D, K, Z
Poles	1P - 4P	1P - 4P	1P - 4P	1P - 4P	1P - 4P	1P - 4P
Max 1pole dimension (in)	2.98x0.68x3.46	2.98x0.68x3.94	2.98x0.68x3.46	3.48x1.04x3.74	3.48x1.04x3.74	2.98x0.68x3.46
Auxilliary contact	yes	yes	yes	yes	yes	yes
Bell alarm	yes	yes	yes	yes	yes	yes
Shunt trip	yes	yes	yes	yes	yes	yes
Bottom-mount aux.contact	yes	-	yes	-	-	yes
Busbars	yes	yes	yes	-	-	yes

ABB