

PRODUCT SPECIFICATION

CTXXW3LS11

Daylite Self-Contained Clear IP65 Naveo Surface

Catalogue Number **CTXXW3LS11**
GID **7TCA091180R0356**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Plastic**
Colour **White**
Dimensions (LxWxD) **342 x 98 x 72 mm**
Temperature Range **0 to 30°C**
Weight **0.86 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **Naveo®Pro**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **251**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single Sided**
Exit Sign Viewing/Recognition Distance (m) **23**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **6.1 VA / 3.9 Watts**
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

- RSEN2X** Down ISO7010 Legend
- RSEN3X** Left ISO7010 Legend
- RSEN6X** Right ISO7010 Legend
- RSEN5X** Up ISO7010 Legend
- RSB1X** Arabic English Legend

XTR Semi-recessing bezel White



Exit Sign
CTXXW3LS11 + RSEN5X



Bulkhead
CTXXW3LS11

