DRAWING NUMBER
D 2501 8004-014

OT600U22

600VAC 600A 4-Pole
Non-Fused Open Type Switch
Rotary operated

cULus Listed, 97C2
Open Type Switch
UL File #101914
CSA Certified, File #58077

Short Circuit Rating at 600VAC		
kA	Fuse/A	Fuse class
100	800	J, T or L
100	600	RK5
35	Circuit Breaker	

3-phase HP Ratings				
VAC	208	240	480	600
HP	150	200	450	500



FRONT VIEW

RIGHT SIDE VIEW



BOTTOM VIEW



Accessories:

Operating Handle
OHB175J12 – Type 1, 3R, 12
OHB175L12 – Type 1, 3R, 4, 4X, 12
Ref. drawing D 2301 8001-001 for pistol grip handle dimensions and installation details.

Terminal Lug Kits
OZXA-800 – 8 lugs
Wire Range:
(2) #2 AWG – 600kcmil
AL7CU, UL Listed

Operating Shaft – Max. encl. depth
OXP12X220 – 12.00 in.
OXP12X280 – 14.50 in.
OXP12X325 – 16.30 in.
OXP12X395 – 19.10 in.
OXP12X465 – 21.80 in.
OXP12X625 – 28.10 in.

Auxiliary Contacts
OA1G10 – 1n.o.
OA3G01 – 1n.c.

REV. LET.	REVISIONS	DATE	REV OR APPD BY

THIS DRAWING IS THE PROPERTY OF ABB Inc. AND CONTAINS PROPRIETARY AND CONFIDENTIAL INFORMATION WHICH MUST NOT BE DUPLICATED, USED OR DISCLOSED OTHER THAN EXPRESSLY AUTHORIZED BY ABB Inc.

ABB Inc.

DATE 14/3/11
DRAWN F. GARCÍA
CHK'D
PROJECT NO.
SHEET 1 OF 1

REV. A

SIZE A

TITLE
OT600U22
4-Pole Non-Fused
Open Type Switch

DRAWING NUMBER
D 2501 8004-014