

# Exit LED edgelit Signature exit LED edgelit surface mount



## Range

Signature range

## Product group

Exit LED edgelit

## Features

- 3 year warranty
- High emergency classification
- LED technology 100,000 hours lamp life
- High temperature NiMH batteries
- Architecturally pleasing slim line design
- One-box solution, overall light weight and snap n' clip mechanism allows for quick and easy installation
- Surface mounted - suitable for ceilings where a recessed fitting is not feasible
- Includes all pictograph diffuser options
- Suspended, wall and cantilever mounting kit options available



## Standard products

Catalogue no.	Description
PLSLED	LED legend surface mount pictograph edgelight

## Accessories

Catalogue no.	Description
PLSLEDCLKIT	Cantilever mounting kit
PLSLEDWMKIT	Wall mounting kit

## Spare parts

Catalogue no.	Description
03-01213P	Battery 4 cell NiMH 4.8V 1.25Ah

## Dimensions

Length	Width	Height (incl. bracket)
375.5mm	79mm	220mm

## Weight

Model	Weight
Standard	2.1kg

## Construction

Part	Construction
Visible housing	White powder coated zinc steel
Diffuser	Moulded acrylic
Non-visible housing	Plastic

## Light source

Model	Light source
Standard	Multiple LED 1.0W

## Power consumption

Model	Power consumption
Standard	2.32W

## Photometrics

Model	Class	Classification
Standard	C0	D3.2
	C90	E2

**Note:** Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

**ABB Australia Pty Limited**

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

**[www.stanilite.com.au](http://www.stanilite.com.au)**

**Note:** We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB  
All rights reserved