

PLC AUTOMATION

Product information

CP600 platform FW / programming SW Overview



CP600 platform control panels, relevant production indexes, FW versions and suitable PB610 versions.

—
CP600 platform

This document summarizes the FW / SW versions and production indexes from the CP600 platform control panels. It informs about the dependencies between devices/FW/SW versions.

Any liability of ABB – regardless of the legal grounds – shall be excluded. In particular any warranty or defect liability for the Products (whether hardware, software or firmware) or for any documentation or information related thereto and any damage or losses resulting there from shall be excluded, e.g. in view of correctness, completeness, applicability of the Products/documentation/information or the same not being up-to-date and free of any defect.

CP600-eCo, CP600 and CP600-Pro: Dependencies between devices, FW, SW

Product	In- dex	Order code	Product line	Operating system (OS)	Board Package	Support BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP604	A0	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.0.161 BASIC	1.2.0/1.2.1 1.2.2	n. a.
CP604	A0	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.0.215 BASIC	1.2.3	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.1.243	1.2.4	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.
CP604	A1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.1.447	2.2.4	n. a.
CP604	D1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP604	D1	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP604	D2	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP604	E0	1SAP504100R0001	CP600- eCo	Linux 3.12	UN60	V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP604-B	A1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP604-B	A1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package	BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP604-B	A1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.
CP604-B	A1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.
CP604-B	A1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.1.447	2.2.4	n. a.
CP604-B	D1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP604-B	D1	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP604-B	D2	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP604-B	E0	1SAP504100R2001	CP600- eCo	Linux 3.12	UN60	V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP607	A0	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.0.161 BASIC	1.2.0/1.2.1 1.2.2	n. a.
CP607	A0	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.1.215 BASIC	1.2.3	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.1.243	1.2.4	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP607	A1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.1.447	2.2.4	n. a.
CP607	D1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP607	D1	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP607	D2	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60 V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP607	E0	1SAP507100R0001	CP600- eCo	Linux 3.12	UN60 V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP607-B	A1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP607-B	A1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.
CP607-B	A1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.
CP607-B	A1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.
CP607-B	A1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.1.447	2.2.4	n. a.
CP607-B	D1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP607-B	D1	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP607-B	D2	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP607-B	E0	1SAP507100R2001	CP600- eCo	Linux 3.12	UN60 V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP610	A0	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.0.0.161 BASIC	1.2.0/1.2.1 1.2.2	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package	BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP610	A0	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.1.215 BASIC	1.2.3	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.0.1.243	1.2.4	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.
CP610	A1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.1.447	2.2.4	n. a.
CP610	D1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP610	D1	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP610	D2	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP610	E0	1SAP510100R0001	CP600- eCo	Linux 3.12	UN60	V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP610-B	A1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP610-B	A1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.6.1.175	2.1.2	n. a.
CP610-B	A1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60	V1.0.0	V1.0.8	V2.8.0.367	2.2.0/2.2.1	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP610-B	A1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.0.424	2.2.2/2.2.3	n. a.
CP610-B	A1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.0	V1.0.8	V2.8.0.447	2.2.4	n. a.
CP610-B	D1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V2.8.1.447	2.4.0	n.a.
CP610-B	D1	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.344	V1.0.10	V4.0.1.462	2.4.1	n.a.
CP610-B	D2	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.0.808	V1.0.11	V4.0.1.462	2.4.1	n.a.
CP610-B	E0	1SAP510100R2001	CP600- eCo	Linux 3.12	UN60 V1.3.718	V1.0.11	V4.5.0.632	2.6.0	n.a.
CP620	A0	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.38	n. a.	V1.58.0.22	n. a.	n. a.
CP620	A1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.
CP620	B0	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.
CP620	B1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP620	B2	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP620	C1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP620	C2	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP620	C3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP620	D1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP620	G1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP620	H1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP620	K1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP620	K1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP620	K1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP620	A1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.
CP620	B0	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.
CP620	B1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP620	B2	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP620	C1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP620	C2	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP620	C3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP620	D1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP620	G1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP620	H1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V4.0.1.462	2.4.1	n. a.
CP620- WEB	A0	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.38	n. a.	n. a.	n. a.	V1.5.15.122
CP620- WEB	A1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	n. a.	n. a.	V1.5.15.122
CP620- WEB	B0	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.125
CP620- WEB	B1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.131b
CP620- WEB	C1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP620- WEB	C2	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP620- WEB	D1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP620- WEB	H1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP620- WEB	K1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP630	A0	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.38	n. a.	V1.58.0.22	n. a.	n. a.
CP630	A1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.
CP630	B0	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.
CP630	B1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP630	B2	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP630	C1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP630	C2	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP630	C3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP630	D1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP630	G1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP630	H1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP630	K1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP630	K1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP630	K1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP630	K1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP630- WEB	A0	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.38	n. a.	n. a.	n. a.	V1.5.15.122

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP630- WEB	A1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	n. a.	n. a.	V1.5.15.122
CP630- WEB	B0	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.125
CP630- WEB	B1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.131b
CP630- WEB	C1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP630- WEB	C2	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP630- WEB	D1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b
CP630- WEB	H1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP630- WEB	K1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP635	A0	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.38	n. a.	V1.58.0.22	n. a.	n. a.
CP635	A1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.
CP635	B0	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP635	B1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP635	B2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP635	C1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635	C2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635	C3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635	D1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP635	G1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP635	H1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635	H2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP635	K1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP635	K1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP635	K1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP635	A1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.
CP635	B0	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.
CP635	B1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP635	B2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP635	C1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635	C2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP635	C3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635	D1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP635	G1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP635	H1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635	H2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V4.0.1.462	2.4.1	n. a.
CP635-B	A1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	V1.58.0.22	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP635-B	B0	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.58.0.22	n. a.	n. a.
CP635-B	B1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.1	n. a.	n. a.
CP635-B	B2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	V1.80.2	n. a.	n. a.
CP635-B	C1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635-B	C2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635-B	C3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	V1.90.0	n. a.	n. a.
CP635-B	D1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP635-B	G1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP635-B	H1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635-B	H2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser	
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP635-B	K1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP635-B	K1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP635-B	K1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V2.31	n. a.	V2.8.1.424	2.2.4	n. a.
CP635-B	K1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31	V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP635-FB	D1	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser	
CP635-FB	D1	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP635-FB	D1	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP635-FB	D1	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP635-FW	D1	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP635-FW	D1	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP635-FW	D1	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP635-FW	D1	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30	V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP635- WEB	A0	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31	V1.38	n. a.	n. a.	n. a.	V1.5.15.122

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP635- WEB	A1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.45	n. a.	n. a.	n. a.	V1.5.15.122
CP635- WEB	B0	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.125
CP635- WEB	B1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.54	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	C1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	C2	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.66	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	D1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	H1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	H2	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP635- WEB	K1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP650	A0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	V1.58.0.22	n. a.	n. a.
CP650	B0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.58.0.22	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP650	B1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.1	n. a.	n. a.
CP650	B2	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.2	n. a.	n. a.
CP650	C0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.80.2	n. a.	n. a.
CP650	C1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.
CP650	C2	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.
CP650	D1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	V1.90.0.975	n. a.	n. a.
CP650- WEB	A0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	n. a.	n. a.	V1.5.15.122
CP650- WEB	B0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	n. a.	n. a.	V1.5.15.125
CP650- WEB	C0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.125
CP650- WEB	C1	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.131b
CP650- WEB	D1	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	n. a.	n. a.	V1.5.15.131b

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP651	A0	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.90.0.975	n.a.	n. a.
CP651	B1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP651	C1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP651	C2	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP651	D1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP651	D1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP651	D1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP651	D1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP651- WEB	A0	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b
CP651- WEB	C1	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP651- WEB	C2	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP651- WEB	D1	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP660	A0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	V1.58.0.22	n. a.	n. a.
CP660	B0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.58.0.22	n. a.	n. a.
CP660	B1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.1	n. a.	n. a.
CP660	B2	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.2	n. a.	n. a.
CP660	C0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.80.2	n. a.	n. a.
CP660	C1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP660	C2	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.
CP660	D1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	V1.90.0.975	n. a.	n. a.
CP660- WEB	A0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	n. a.	n. a.	V1.5.15.122
CP660- WEB	B0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	n. a.	n. a.	V1.5.15.125
CP660- WEB	C0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.125
CP660- WEB	C1	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.131b
CP660- WEB	D1	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	n. a.	n. a.	V1.5.15.131b
CP661	A0	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.90.0.975	n.a.	n. a.
CP661	B1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP661	C1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP661	C2	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP661	D1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP661	D1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP661	D1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP661	D1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP661- WEB	A0	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b
CP661- WEB	C1	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP661- WEB	C2	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP661- WEB	D1	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP665	A0	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.90.0.975	n. a.	n. a.
CP665	B1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP665	C1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP665	C2	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP665	D1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP665	D1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP665	D1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP665	D1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP665- WEB	A0	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	n. a.	n. a.	V1.5.15.131b
CP665- WEB	C1	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP665- WEB	C2	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n. a.	n. a.	V1.5.15.131b
CP665- WEB	D1	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	n. a.	n. a.	V1.5.15.131b
CP675	A0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	V1.58.0.22	n. a.	n. a.
CP675	B0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.58.0.22	n. a.	n. a.
CP675	B1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.1	n. a.	n. a.
CP675	B2	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	V1.80.2	n. a.	n. a.
CP675	C0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.80.2	n. a.	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP675	C1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.
CP675	C2	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	V1.90.0	n. a.	n. a.
CP675	D1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	V1.90.0.975	n. a.	n. a.
CP675- WEB	A0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.58	n. a.	n. a.	n. a.	V1.5.15.122
CP675- WEB	B0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.65	n. a.	n. a.	n. a.	V1.5.15.125
CP675- WEB	C0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.125
CP675- WEB	C1	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.73	n. a.	n. a.	n. a.	V1.5.15.131b
CP675- WEB	D1	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20 V2.80	n. a.	n. a.	n. a.	V1.5.15.131b
CP676	A0	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.90.0.975	n.a.	n. a.
CP676	B1	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	V1.91.0	1.1.1	n. a.
CP676	C1	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.0.161	1.2	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.0.1.243	1.2.3	n. a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.4.0.89	2.0.0/2.0.1 2.0.2	n. a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n. a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	V2.6.1.175	2.1.2	n. a.
CP676	D1	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.367	2.2.0/2.2.1	n. a.
CP676	D1	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.0.424	2.2.2/2.2.3	n. a.
CP676	D1	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V2.8.1.447	2.2.4	n. a.
CP676	D1	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	V4.0.1.462	2.4.1	n. a.
CP676- WEB	A0	1SAP576200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.76	n. a.	n.a.	n.a.	V1.5.15.131b
CP676- WEB	C1	1SAP576200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V1.96	n. a.	n.a.	n.a.	V1.5.15.131b
CP676- WEB	D1	1SAP576200R0001	CP600	Win Embedd. CE 6.0 Core	UN30 V2.31	n. a.	n.a.	n.a.	V1.5.15.131b

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP6407	A0	1SAP540710R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.2.4	n. a.
CP6407	A1	1SAP540710R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.4.1	n. a.
CP6407	A1	1SAP540710R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V4.0.1.462	2.4.1	n. a.
CP6407	A2	1SAP540710R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.809	V1.0.2	V4.0.1.462	2.4.1	n. a.
CP6407	B0	1SAP540710R0001	CP600 2nd G	Linux 3.12	UN60 V1.3.718	V1.0.2	V4.5.0.632	2.6.0	n.a.
CP6410	A0	1SAP541010R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.2.4	n. a.
CP6410	A1	1SAP541010R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.4.1	n. a.
CP6410	A1	1SAP541010R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V4.0.1.462	2.4.1	n. a.
CP6410	A2	1SAP541010R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.809	V1.0.2	V4.0.1.462	2.4.1	n. a.
CP6410	B0	1SAP541010R0001	CP600 2nd G	Linux 3.12	UN60 V1.3.718	V1.0.2	V4.5.0.632	2.6.0	n.a.
CP6415	A0	1SAP541510R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.2.4	n. a.
CP6415	A1	1SAP541510R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V2.8.1.477	2.4.1	n. a.
CP6415	A1	1SAP541510R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.538	V1.0.1	V4.0.1.462	2.4.1	n. a.
CP6415	A2	1SAP541510R0001	CP600 2nd G	Linux 3.12	UN80 V1.0.809	V1.0.2	V4.0.1.462	2.4.1	n. a.
CP6415	B0	1SAP541510R0001	CP600 2nd G	Linux 3.12	UN60 V1.3.718	V1.0.2	V4.5.0.632	2.6.0	n.a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser	
CP6605	A0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.298	V1.0.1	V2.6.1.126	n.a.	n. a.
CP6605	A0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.298	V1.0.3	V2.6.1.175	2.1.2	n. a.
CP6605	A0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.298	V1.0.3	V2.8.0.367	2.2.0/2.2.1	n. a.
CP6605	A0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.298	V1.0.3	V2.8.0.424	2.2.2/2.2.3	n. a.
CP6605	A0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.298	V1.0.3	V2.8.1.447	2.2.4	n. a.
CP6605	B0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN70	V1.0.808	V1.0.7	V2.8.1.447	2.2.4	n. a.
CP6605	C0	1SAP560510R0001	CP600- Pro	Linux 3.12	UN60	V1.3.718	V1.0.7	V4.5.0.632	2.6.0	n. a.
CP6607	A0	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.126	n.a.	n. a.
CP6607	A0	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.175	2.1.2	n. a.
CP6607	A0	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.367	2.2.0/2.2.1	n. a.
CP6607	A0	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.424	2.2.2/2.2.3	n. a.
CP6607	B1	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.15	V2.8.0.424	2.2.3	n. a.
CP6607	B1	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.15	V2.8.1.447	2.2.4	n. a.
CP6607	D1	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.22	V2.8.1.447	2.4.1	n. a.
CP6607	D1	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.22	V4.0.1.462	2.4.1	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser
CP6607	D2	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65 V1.0.743	V1.0.22	V4.0.1.462	2.4.1	n. a.
CP6607	D3	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65 V1.0.743	V1.0.25	V4.0.1.462	2.4.1	n. a.
CP6607	D4	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65 V1.0.758	V1.0.25	V4.0.1.462	2.4.1	n. a.
CP6607	D6	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65 V1.0.829	V1.0.26	V4.0.1.462	2.4.1	n. a.
CP6607	E0	1SAP560710R0001	CP600- Pro	Linux 3.12	UN65 V1.3.717	V1.0.26	V4.5.0.632	2.6.0	n. a.
CP6610	A0	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.10	V2.6.1.126	n.a.	n. a.
CP6610	A0	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.10	V2.6.1.175	2.1.2	n. a.
CP6610	A0	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.10	V2.8.0.367	2.2.0/2.2.1	n. a.
CP6610	A0	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.10	V2.8.0.424	2.2.2/2.2.3	n. a.
CP6610	B1	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.15	V2.8.0.424	2.2.3	n. a.
CP6610	B1	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.304	V1.0.15	V2.8.1.447	2.2.4	n. a.
CP6610	D1	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.387	V1.0.22	V2.8.1.447	2.4.1	n. a.
CP6610	D1	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.387	V1.0.22	V4.0.1.462	2.4.1	n. a.
CP6610	D2	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.743	V1.0.22	V4.0.1.462	2.4.1	n. a.
CP6610	D3	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65 V1.0.743	V1.0.25	V4.0.1.462	2.4.1	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser	
CP6610	D4	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65	V1.0.758	V1.0.25	V4.0.1.462	2.4.1	n. a.
CP6610	D6	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65	V1.0.829	V1.0.26	V4.0.1.462	2.4.1	n. a.
CP6610	E0	1SAP561010R0001	CP600- Pro	Linux 3.12	UN65	V1.3.717	V1.0.26	V4.5.0.632	2.6.0	n. a.
CP6615	A0	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.126	n. a.	n. a.
CP6615	A0	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.175	2.1.2	n. a.
CP6615	A0	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.367	2.2.0/2.2.1	n. a.
CP6615	A0	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.424	2.2.2/2.2.3	n. a.
CP6615	B1	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.15	V2.8.0.424	2.2.3	n. a.
CP6615	C1	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.18	V2.8.0.424	2.2.3	n. a.
CP6615	C1	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.18	V2.8.1.447	2.2.4	n. a.
CP6615	D1	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.23	V2.8.1.447	2.4.1	n. a.
CP6615	D1	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.23	V4.0.1.462	2.4.1	n. a.
CP6615	D2	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.743	V1.0.24	V4.0.1.462	2.4.1	n. a.
CP6615	D4	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.758	V1.0.25	V4.0.1.462	2.4.1	n. a.
CP6615	D6	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.0.829	V1.0.26	V4.0.1.462	2.4.1	n. a.

Product	In- dex	Order code	Product line	Operating system (OS)	Board Support Package BSP	Boot- loader	PB610	Autom. Builder	Micro- browser	
CP6615	E0	1SAP561510R0001	CP600- Pro	Linux 3.12	UN65	V1.3.717	V1.0.26	V4.5.0.632	2.6.0	n. a.
CP6621	A0	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.126	n.a.	n. a.
CP6621	A0	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.6.1.175	2.1.2	n. a.
CP6621	A0	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.367	2.2.0/2.2.1	n. a.
CP6621	A0	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.10	V2.8.0.424	2.2.2/2.2.3	n. a.
CP6621	B1	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.15	V2.8.0.424	2.2.3	n. a.
CP6621	C1	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.18	V2.8.0.424	2.2.3	n. a.
CP6621	C1	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.304	V1.0.18	V2.8.1.447	2.2.4	n. a.
CP6621	D1	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.23	V2.8.1.447	2.4.1	n. a.
CP6621	D1	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.387	V1.0.23	V4.0.1.462	2.4.1	n. a.
CP6621	D2	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.743	V1.0.24	V4.0.1.462	2.4.1	n. a.
CP6621	D4	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.758	V1.0.25	V4.0.1.462	2.4.1	n. a.
CP6621	D6	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.0.829	V1.0.26	V4.0.1.462	2.4.1	n. a.
CP6621	E0	1SAP562110R0001	CP600- Pro	Linux 3.12	UN65	V1.3.717	V1.0.26	V4.5.0.632	2.6.0	n. a.

ABB AG
Eppelheimer Straße 82
D-69123 Heidelberg / Germany
Tel.: +49 62 21 701 1444
Fax: +49 62 21 701 1382

abb.com/plc

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.
Copyright© 2024 ABB
All rights reserved