

PRODUCT SPECIFICATION

CTSR2-SAM3-D1

Serenga 2 Self-Contained Open Area IP54 Naveo Surface

Catalogue Number **CTSR2-SAM3-D1**
GID **7TCA091180R0235**

Warranty **4 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling Surface**
Housing Material **Aluminium/Plastic**
Colour **White**
Dimensions (LxWxD) **150 x 150 x 35 mm**
Temperature Range **5 to 40°C**
Weight **0.961 Kg**

Nominal Voltage **220-240v AC 50Hz**
Emergency Duration (Hours) **3 Hours**
Battery **NiMH**
Monitoring Equipment **Naveo test**
Lamp **1 x 2W LED**
Light output in Emergency Operation **203 Lumens**
Average Lifespan light source (hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 5600 / 70**
Degree of Protection **IP 54 IK tbc**

Wiring System **Maintained / non-maintained circuit**
Type of Legend **Not Applicable**
Exit Sign Viewing/Recognition Distance (m) **Not Applicable**
Power Consumption **3.5 VA / 3 Watts**
Nominal Current **15 (mA)**
Inrush Current **tbc A to 0.1 ms**

Accessories

- SR2-LENS1** Lens A Escape route 2-4M Ceiling mount
- SR2-LENS2** Lens B Escape route 4-8M Ceiling mount OR Spot 2-4M Ceiling mount
- SR2-LENS3** Lens C Escape route 8-12M Ceiling mount
- SR2-LENS4** Lens D Open Area 2-4M Ceiling mount
- SR2-LENS5** Lens E Open Area 4-8M Ceiling mount
- SR2-LENS6** Lens E Open Area 8-12M Ceiling mount
- SR2-LENS7** Lens G Escape route 2-4M Wall mount

