

PRODUCT TRAINING

T&B® Fittings

Industrial fittings

Boost your sales by learning about the innovations your customers need.



Welcome to ABB Installation Products industrial fittings training.

Inside this box, you'll find representative samples of some of the innovative products that make the ABB T&B® Fittings brand an industry leader in fittings for rigid, IMC and flexible conduit as well as portable cord.

Featured products



Blackjack® grounding bushing

The versatile choice for threaded or threadless IMC or rigid metallic conduit.

- 21 SKUs cover the full offering of threaded or threadless conduit, 105 °C and 150 °C, copper or aluminum wire, as compared to 140+ SKUs with other manufacturers
- Integral ground lug provides superior bonding and grounding
- Smooth dipped insulator provides superior wire protection and pull glide



T&B® hub

Use with threaded rigid conduit or IMC in wet or dry locations, indoors or out.

- Innovative sealing ring and groove design outperform standard O-ring design and seal even if conduit run isn't perpendicular to enclosure
- Innovative body design enables installer to achieve desired torque with wrench or screwdriver and hammer
- UL 94V-0, 105 °C insulated throat protects wire insulation and creates a watertight union

Industrial fittings product training

Boost your sales by learning about the innovations your customers need.



BlueKote® conduit bodies

Industrial-grade corrosion protection for use with rigid conduit and IMC.

- 4.5 mils of external and 6.5 mils of internal coating protection provide superior corrosion resistance
- Internal PTFE coating facilitates easier, safer wire pulling
- Universal LU eliminates the need for LB, LR, LL and inspection C conduit bodies
- U-shape provides great glide when pulling wires



T&B Liquidtight Systems® flexible metallic conduit fittings

Choose the right liquid-tight fitting solution for flexible, metallic-cored conduit.

- “Umbrella” design of gland nut pushes liquids away from enclosure — no pooling
- Double-beveled sealing ring provides custom conformity around conduit
- Safe Edge® ground cone offers excellent contact for superior bonding and pull-out resistance
- Available in steel, iron, aluminum, non-metallic, stainless steel and nickel-plated brass
- UL listed for Type 6 (temporary submersion), giving you the peace of mind your enclosure is protected
- Heat-curved insulator provides wire protection and glide
- Many varieties are UL listed Type 4 and 4X for superior water and corrosion protection



Ranger® cord fittings

Range-taking cable glands for cord and cable.

- Available in steel, aluminum, stainless steel and non-metallic materials
- UL listed for Type 6 (temporary submersion), giving you the peace of mind your enclosure is protected
- Range-taking capabilities enable 9 sizes to replace 15 or 16 other manufacturers’ sizes
- Many varieties UL listed Type 4 and 4X providing superior protection from moisture and corrosion