



SER-EC

Slave, maintained surface mount luminaire module series Serenga

Product Information

Type	SER-EC
Catalog number	32110200
Category_	Combined luminaire;Escape route signalisation
GTIN	08713812073279
GID	7TCA091130R0053
Serie	serenga
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	Gray
Material	Aluminium / polycarbonate
Colour	Gray
Length (mm)	293
Width (mm)	69
Height/depth (mm)	74
Nominal voltage (V)	230
Voltage type	AC/DC
Monitoring equipment	None
With lamp	No
Protection class	II
Degree of protection (IP)	20
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Other
Circuit	Other
Power consumption maintained mode (W)	3,5
Apparent power consumption maintained mode (VA)	8
Nominal current (mA)	35
Inrush Current (A - 0.1ms)	22,5
Powerfactor	0,44
Temperature range (°C)	5 ~ +25

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces

Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,6
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	297 x 128 x 71