



中国国家强制性产品认证证书

证书编号：2024010302658030

认证委托人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产者名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、型号、规格

隔离开关熔断器组

OS32GB_, OS32GD_, OS50GF_, OS60GJ_, OS63GB_, OS63GD_; 详见参数附页

产品标准和技术要求

GB/T 14048.3-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 15 日 有效期至：2029 年 07 月 14 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站 (www.cnca.gov.cn) 查询。



签发：

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





中国国家强制性产品认证证书

证书编号: 2024010302658030

证书附页: 第 1 页 共 2 页

OS32GB_, OS32GD_, OS50GF_, OS60GJ_, OS63GB_, OS63GD_

Uimp: 12kV;

Ui: 1000V;

Ith: 32A(OS32GB, OS32GD), 50A(OS50GF), 60A(OS60GJ), 63A(OS63GB, OS63GD);

Ue: AC415V, AC500V, AC690V;

Ie: 32A(OS32GB, OS32GD), 50A(OS50GF), 60A(OS60GJ), 63A(OS63GB, OS63GD);

Iq: OS50GF: 3P, 4P: 50kA(415V), 100kA(500V), 80kA(690V);

OS32GD, OS63GD: 2P: 100kA(500V), 80kA(690V);

3P, 4P: 50kA(415V), 100kA(500V), 50kA(690V), 80kA(690V);

OS32GB, OS63GB: 2P: 80kA(415V);

3P, 4P: 50kA(415V), 80kA(415V);

OS60GJ: 3P, 4P: 100kA(500V);

使用类别: AC-21A, AC-22A, AC-23A;

极数: 2P, 3P, 4P;

适用频率: 50/60Hz;

IP20(仅对前面板)

型号解释:

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



中国国家强制性产品认证证书

证书编号: 2024010302658030

证书附页: 第 2 页 共 2 页

OS	32	G	D	S	04	F	H	K	
									P=handle&shaft included 标配柜外安装手柄和转轴 K=direct handle 标配直接安装手柄 Blank=without handle&shaft 空白=不带手柄和转轴
									H=sliver layer 20μ 镀银 20μ
									Fourth pole 第四极 F=fused neutral 熔断器中性极 N1=switched neutral on left side 开关中性极 (位于开关左侧) N2=switched neutral on right side 开关中性极 (位于开关右侧)
									Poles(according to side of mechanism) 极数 2 poles(2 极)- 02 20 11 3 poles(3 极)- 03 30 12 or 21 4 poles(4 极)- 04 40 13 31 or 22 1 Number= number of poles on left side 第一位数字表示在机械结构左边的极数 2 Number= number of poles on right side 第二位数字表示在机械结构右边的极数
									操作机构位置 S=side operated 侧面操作 Blank=front operated 正面操作
									Type of fuse holder 熔断器支持件型号 F=NFC,14X51(OS50_only) D=DIN000 (OS32_OS63_only) B=BS88,A2-A3 (OS32_OS63_only) J=UL, type J 60A fuse(OS60_only)
									Construction 结构 G=Gamma
									Rated current: 32,50,63,60 电流等级(A)
									OS= switch-disconnector-fuse 隔离开关熔断器组型号

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2024010302658030

NAME AND ADDRESS OF THE APPLICANT

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

NAME AND LOCATION OF THE FACTORY

ABB Oy
Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME,MODEL AND SPECIFICATION

Switch-disconnector-fuse
OS32GB_, OS32GD_, OS50GF_, OS60GJ_, OS63GB_, OS63GD_;See the Appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

This is to certify that the above mentioned product(s) complies with the requirements of
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jul.15,2024

Valid until: Jul.14,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2024010302658030

Appendix: Page 1 of 1

OS32GB_, OS32GD_, OS50GF_, OS60GJ_, OS63GB_, OS63GD_
Uimp: 12kV;
Ui: 1000V;
Ith: 32A(OS32GB, OS32GD), 50A(OS50GF), 60A(OS60GJ), 63A(OS63GB, OS63GD);
Ue: AC415V, AC500V, AC690V;
Ie: 32A(OS32GB, OS32GD), 50A(OS50GF), 60A(OS60GJ), 63A(OS63GB, OS63GD);
Iq: OS50GF: 3P, 4P: 50kA(415V), 100kA(500V), 80kA(690V);
OS32GD, OS63GD: 2P: 100kA(500V), 80kA(690V);
3P, 4P: 50kA(415V), 100kA(500V), 50kA(690V), 80kA(690V);
OS32GB, OS63GB: 2P: 80kA(415V);
3P, 4P: 50kA(415V), 80kA(415V);
OS60GJ: 3P, 4P: 100kA(500V);
Utilization Category: AC-21A, AC-22A, AC-23A;
Poles: 2P, 3P, 4P;
50/60Hz;
IP20(Only on the front panel)

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.