



EVA-R-CLI

Slave 2 watt, 230 Volt round white recess led luminaire, series Evago. Light distribution: long (L), for example hallways

Product Information

Type	EVA-R-CLI
Catalog number	5520257061
Category_	Escape route lighting
GTIN	08713812762814
GID	7TCA091130R0389
Serie	Evago
Warranty (Year)	5



Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Aluminium / plastic
Colour housing	White
Material	Aluminium / polycarbonate
Colour	White
Length (mm)	226
Width (mm)	100
Height/depth (mm)	38
Maximum outer diameter (mm)	100
Built-in length (mm)	226
Built-in width (mm)	68
Built-in diameter (mm)	68
Built-in depth (mm)	35
Nominal voltage (V)	230
Voltage type	AC
Monitoring equipment	None
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	203
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	42
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	5
Apparent power consumption maintained mode (VA)	5,5
Nominal current (mA)	24
Inrush Current (A - 0.1ms)	3

Powerfactor	0,9
Temperature range (°C)	0 ~ +40

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30405
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,315
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	225 x 170 x 62