TYPICAL WIRING DIAGRAM

CONNECT LINE WIRES TO PROPER TERMINALS ON RECEPTACLE



LISTED
POWER OUTLET
66FL

USE COPPER WIRE ONLY

USE ONLY 60 DEG.C (140 DEG.F) CONDUCTORS ON ALL FIELD INSTALLED LINE, LOAD AND NEUTRAL TERMINATIONS.

WIRE RANGE		
CONNECTOR	COPPER	
	SOLID	STRANDED
LINE-DUPLEX	14-10	14-10
LOAD-VIA RECEPT./PLUG	14-10	14-10
NEUTRAL-DUPLEX	14-10	14-10
EQUIP.GRD.-GL3	12-8	12-2

LUG TIGHTENING TORQUE (LB-IN)

SCREW TYPE	WIRE SIZE	TORQUE
SLOT	14-10	32-35
	8	36-40
	6-4	41-45
	3-2/0	45-50

RAINPROOF POWER INLET

MODEL NO. U050ND

50 AMPS

120/240 VOLTS A-C

TYPE 3R ENCLOSURE

WHEN CABINET HAS PROVISION FOR A CONDUIT HUB, SELECT FROM CHART BELOW.

CONDUIT SIZE	CLOSURE CAP	3/4	1	1 1/4	1 1/2
CAT. NO.	801	807	810	812	815

DANGER

HAZARD OF ELECTRICAL SHOCK OR BURN. TURN OFF POWER BEFORE WORKING INSIDE THIS EQUIPMENT.

MIDWEST ELECTRIC PRODUCTS,INC.
P.O. BOX 910
MANKATO, MN 56002-0910
WWW.MIDWESTELECTRIC.COM

MNP601371

Midwest®