

Hazardous location combo pictogram



CERTIFICATION

CLASS I

Division 2 Group A, B, C, D

CLASS II

Division 1 & 2 Group E, F, G

CLASS III

Contact your ABB sales representative
to verify classification



APPROVALS



Key features and benefits

Certified Class I Division 2, Groups A, B, C and D as per CSA C22 .2
No .137-M1981

Includes the addition of Class II Div 1&2 Groups E, F and G as well as
Class III ratings

Certified temperature Codes for several types of emergency lamps

Polyvinyl chloride frame, with built-in gasket to prevent water
infiltration

Heavy-duty 1/8-inch thick aluminum back plate with key-holes for wall-
mount installation

Sealed, polycarbonate vandal-resistant faceplate

Legend illuminated by long-life white LEDs is warranted for 10 years

Comes standard with two pictogram films for direction selection

Two LED lamps shielded by a clear polycarbonate cover

Sealed, maintenance-free Lead-Calcium or Nickel-Cadmium batteries

Comes standard with auto-test, non audible

Remote load capacity: covers with LED lights 200 ft up to 500 ft of
egress illumination

Cold-weather option: -40°C (-40°F) with only 14W extra power
consumption

Auto-testing capabilities (specific load requirements)

Meets or exceeds CSA C22 .2 No .141-15

DIMENSIONS Dimensions are approximate and subject to change.



< Pictogram
LEFT from here



Pictogram
STRAIGHT from here



Pictogram >
RIGHT from here

