



# 中国国家强制性产品认证证书

证书编号：2024010307654703

认证委托人名称及地址

ABB Stotz-Kontakt GmbH  
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产者名称及地址

ABB Stotz-Kontakt GmbH  
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称及地址

ABB 新会低压开关有限公司  
广东省江门市新会区今古洲工业开发区

产品名称和系列、型号、规格

电动机保护用断路器  
MS165, MO165; 规格参数详见附页

产品标准和技术要求

GB/T 14048. 2-2020; GB/T 14048. 4-2020

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》  
(CNCA-C03-02:2024) 的要求，特发此证。

发证日期：2024 年 07 月 09 日 有效期至：2029 年 07 月 08 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，  
也可在认监委网站 ([www.cnca.gov.cn](http://www.cnca.gov.cn)) 查询。



签发：

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司





# 中国国家强制性产品认证证书

证书编号: 2024010307654703

证书附页: 第 1 页 共 3 页

上报参数:

MS165, MO165

Uimp: 8kV;

Ui: 1000V;

Ue: AC400V, AC690V;

In: 10-16A, 14-20A, 18-25A, 23-32A, 30-42A, 40-54A, 52-65A, 62-73A, 70-80A(MS165);

16A, 20A, 25A, 32A, 42A, 54A, 65, 73, 80A(MO165);

过电流脱扣器类型:热磁式(MS165), 电磁式(MO165);

AC400V:

Ics=Icu=100kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20, MO165-20,

MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B, MS165-32,

MO165-32, MS165-32B, MO165-32B);

Ics=Icu=50kA(MS165-42, MO165-42, MS165-42B, MO165-42B);

Ics=30kA, Icu=50kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65, MO165-65, MS165-65B, MO165-65B);

Ics=Icu=30kA(MS165-73, MO165-73, MS165-80, MO165-80 );

AC690V:

Ics=Icu=10kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20, MO165-20,

MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B, MS165-32,

MO165-32, MS165-32B, MO165-32B, MS165-42, MO165-42, MS165-42B, MO165-42B);

Ics=6kA, Icu=8kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65,

MO165-65, MS165-65B, MO165-65B, MS165-73, MO165-73, MS165-80, MO165-80);

选择性类别: A;

使用类别: AC-3, AC-3e;

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# 中国国家强制性产品认证证书

证书编号: 2024010307654703

证书附页: 第 2 页 共 3 页

适用频率: 50/60Hz;

适用于隔离;

脱扣级别:10;

极数: 3P;

配用的辅助触头:

(HKF1:CQC 证书编号 CQC2010010304397265)

Ith: 5A;

AC-15: Ue/Ie: 24V/3A,120V/3A,240V/1.5A;

DC-13: Ue/Ie: 24V/1A,125V/0.27A, 250V/0.11A;

1NO1NC,2NO;

(SK1, HK1, CK1: CQC 证书编号 CQC2010010304397264)

Ith:6A;

AC-15: Ue/Ie: 24V/6A, 110-120V/6A,220 - 240V/4A,400V/3A,690V/1A;

DC-13: Ue/Ie: 24V/2A,110-125V/0.55A,250V/0.27A,400V/0.15A, 600V/0.15A;

1NO1NC, 2NO, 2NC

本页为证书附页, 应与证书主页同时使用。



中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# 中国国家强制性产品认证证书

证书编号：2024010307654703

证书附页：第 3 页 共 3 页

型号解释：

MS 165 — 16 B  
1 2 3 4

- 1.Product series/产品系列 (MS or MO)。
- 2.Basic Type/基本框架。
3. Current range /电流等级, max. Current/最大电流。
4. B: Railway Application, without B: normal type/  
B: 适用于铁路, 没有 B: 普通型号。

本页为证书附页，应与证书主页同时使用。



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

**CERTIFICATE NO.:** 2024010307654703

**NAME AND ADDRESS OF THE APPLICANT**

ABB Stotz-Kontakt GmbH  
Eppelheimer Strasse 82 69123 Heidelberg Germany

**NAME AND ADDRESS OF THE MANUFACTURER**

ABB Stotz-Kontakt GmbH  
Eppelheimer Strasse 82 69123 Heidelberg Germany

**NAME AND LOCATION OF THE FACTORY**

ABB Xinhui Low Voltage Switchgear Co.,Ltd.  
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province,  
P.R.China

**PRODUCT NAME,MODEL AND SPECIFICATION**

Motor protection circuit breaker  
MS165, MO165; See the Appendix

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.2-2020;GB/T 14048.4-2020

This is to certify that the above mentioned product(s) complies with the requirements of  
implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** Jul.09,2024

**Valid until:** Jul.08,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to  
the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010307654703

Appendix : Page 1 of 2

MS165, MO165

Uimp: 8kV;

Ui: 1000V;

Ue: AC400V, AC690V;

In: 10-16A, 14-20A, 18-25A, 23-32A, 30-42A, 40-54A, 52-65A, 62-73A,  
70-80A(MS165);

16A, 20A, 25A, 32A, 42A, 54A, 65, 73, 80A(MO165);

Over current release type : Thermal Magnetic type (MS165), Electro-magnetic  
(MO165);

AC400V:

Ics=Icu=100kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20,  
MO165-20,

MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B,  
MS165-32,

MO165-32, MS165-32B, MO165-32B);

Ics=Icu=50kA(MS165-42, MO165-42, MS165-42B, MO165-42B);

Ics=30kA, Icu=50kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65,  
MO165-65, MS165-65B, MO165-65B);

Ics=Icu=30kA(MS165-73, MO165-73, MS165-80, MO165-80 );

AC690V:

Ics=Icu=10kA(MS165-16, MO165-16, MS165-16B, MO165-16B, MS165-20,  
MO165-20,

MS165-20B, MO165-20B, MS165-25, MO165-25, MS165-25B, MO165-25B,  
MS165-32,

MO165-32, MS165-32B, MO165-32B, MS165-42, MO165-42, MS165-42B,  
MO165-42B);

Ics=6kA, Icu=8kA(MS165-54, MO165-54, MS165-54B, MO165-54B, MS165-65,

MO165-65, MS165-65B, MO165-65B, MS165-73, MO165-73, MS165-80,  
MO165-80);

Selectivity Category: A;

Utilization Category: AC-3, AC-3e;

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.



# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，  
不得单独使用  
This translated document  
does not have legal validity and  
cannot be used in isolation

CERTIFICATE NO. : 2024010307654703

Appendix : Page 2 of 2

50/60Hz;

Suitable for isolation;

Trip class com.cqc.cms.component.word.CertiAnnexDataModel:10;

Poles: 3P;

Attached Auxiliary Contacts:

(HKF1: CQC2010010304397265)

Ith: 5A;

AC-15: Ue/Ie: 24V/3A,120V/3A,240V/1.5A;

DC-13: Ue/Ie: 24V/1A,125V/0.27A, 250V/0.11A;

1NO1NC,2NO;

(SK1, HK1, CK1: CQC2010010304397264)

Ith:6A;

AC-15: Ue/Ie: 24V/6A, 110-120V/6A,220 - 240V/4A,400V/3A,690V/1A;

DC-13: Ue/Ie: 24V/2A,110-125V/0.55A,250V/0.27A,400V/0.15A, 600V/0.15A;

1NO1NC, 2NO, 2NC

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.