



## SER-EC/24

Slave 24 Volt, maintained surface mount luminaire module series Serenga

### Product Information

|                 |   |
|-----------------|---|
| Type            | SER-EC/24                                     |
| Catalog number  | 32110203                                      |
| Category_       | Combined luminaire;Escape route signalisation |
| GTIN            | 08713812750101                                |
| GID             | 7TCA091130R0059                               |
| Serie           | serenga                                       |
| Warranty (Year) | 5   |



### Characteristics

|   |                                     |
|---|-------------------------------------|
| Power supply system                             | Central                             |
| Continuous operation                            | Yes                                 |
| Mounting Method                                 | Ceiling;Wall                        |
| Mounting form                                   | Surface                             |
| Material housing                                | Aluminium / plastic                 |
| Colour housing                                  | Gray                                |
| Material  | Aluminium / polycarbonate           |
| Colour  | Gray                                |
| Length (mm)                                     | 293                                 |
| Width (mm)                                      | 69                                  |
| Height/depth (mm)                               | 74                                  |
| Nominal voltage (V)                             | 24                                  |
| Voltage type                                    | AC/DC                               |
| Monitoring equipment                            | None                                |
| With lamp                                       | No                                  |
| Protection class                                | II                                  |
| Degree of protection (IP)                       | 20                                  |
| With remote switch connection                   | No                                  |
| Wiring system                                   | Maintained / non-maintained circuit |
| Type of indicator                               | Single / double-sided               |
| Labelling type                                  | Other                               |
| Circuit   | Other                               |
| Power consumption maintained mode (W)           | 4,9 / 5,0                           |
| Apparent power consumption maintained mode (VA) | 7,7 / 5,0                           |
| Nominal current (mA)                            | 290 / 189                           |
| Inrush Current (A - 0.1ms)                      | 7 / 4,5                             |
| Powerfactor                                     | 0,65                                |
| Temperature range (°C)                          | 5 ~ +25                             |

### Article Details

|                 |                     |
|-----------------|---------------------|
| Product class   | Emergency luminaire |
| E-code          | EC001957            |
| Discount group  | 30405               |
| Harmonized code | 9405408440          |
| GLN             | 8713812000008       |

### Ordering information

|            |        |
|------------|--------|
| Orderable  | Yes    |
| Order-Unit | Pieces |

|                        |   |
|------------------------|---|
| Minimum order quantity | 1 |
| Order Increment        | 1 |

**Supply Information**

|                                   |                |
|-----------------------------------|----------------|
| Weight (kg)                       | 0,935          |
| Packaging                         | Cardboard box  |
| Packaging dimensions (LxWxH) (mm) | 297 x 128 x 71 |