

Spec-Kon® cable ties

The right cable tie for the right application

Characteristics


A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	Natural
Flammability rating	UL 94 V-2
Other properties	Halogen free, Silicone free

GID-Ordering code	Product Ref.	Length	Width	Min. tensile strength	Bundle diameter from... to...	Quantity	Bags/ Carton
		L	W				
		[mm]	[mm]	[N]	[mm]	[pieces]	
7TCA300020R0000	SKT100-80-100	100	2.5	80	1.5 - 22	100	550
7TCA300040R0000	SKT100-80	100	2.5	80	1.5 - 22	1000	70
7TCA300020R0001	SKT140-80-100	140	2.5	80	1.5 - 33	100	450
7TCA300040R0001	SKT140-80	140	2.5	80	1.5 - 33	1000	55
7TCA300020R0002	SKT160-80-100	160	2.5	80	1.5 - 40	100	400
7TCA300040R0002	SKT160-80	160	2.5	80	1.5 - 40	1000	45
7TCA300020R0003	SKT200-80-100	200	2.5	80	1.5 - 53	100	300
7TCA300040R0003	SKT200-80	200	2.5	80	1.5 - 53	1000	32
7TCA300100R0000	SKT140-180-100	140	3.6	180	2 - 33	100	300
7TCA300120R0000	SKT140-180	140	3.6	180	2 - 33	1000	30
7TCA300100R0001	SKT200-180-100	200	3.6	180	2 - 53	100	200
7TCA300120R0001	SKT200-180	200	3.6	180	2 - 53	1000	22
7TCA300100R0002	SKT300-180-100	300	3.6	180	2 - 76	100	120
7TCA300120R0002	SKT300-180	300	3.6	180	2 - 76	1000	12
7TCA300100R0003	SKT370-180-100	370	3.6	180	2 - 102	100	120
7TCA300120R0003	SKT370-180	370	3.6	180	2 - 102	1000	12
7TCA300180R0000	SKT188-220-100	188	4.8	220	3 - 46	100	160
7TCA300200R0000	SKT188-220	188	4.8	220	3 - 46	1000	16
7TCA300180R0001	SKT215-220-100	215	4.8	220	3 - 53	100	11
7TCA300200R0001	SKT215-220	215	4.8	220	3 - 53	1000	13
7TCA300180R0002	SKT250-220-100	250	4.8	220	3 - 60	100	120
7TCA300200R0002	SKT250-220	250	4.8	220	3 - 60	1000	12
7TCA300180R0003	SKT300-220-100	300	4.8	220	3 - 76	100	80
7TCA300200R0003	SKT300-220	300	4.8	220	3 - 76	1000	8
7TCA300180R0004	SKT370-220-100	370	4.8	220	3 - 102	100	70
7TCA300200R0004	SKT370-220	370	4.8	220	3 - 102	1000	7
7TCA300260R0000	SKT300-540-100	300	7.6	540	7 - 76	100	50
7TCA300280R0000	SKT300-540	300	7.6	540	7 - 76	500	10
7TCA300260R0001	SKT370-540-100	370	7.6	540	7 - 102	100	40
7TCA300280R0001	SKT370-540	370	7.6	540	7 - 102	500	8
7TCA300260R0003	SKT450-540-50	450	7.6	540	7 - 142	50	50
7TCA300260R0002	SKT750-540-50	750	7.6	540	7 - 218	50	30
7TCA300340R0000	SKT776-780-50	776	9.0	780	7 - 228	50	30
7TCA300340R0001	SKT912-780-50	912	9.0	780	7 - 263	50	10



Spec-Kon® cable ties

The right cable tie for the right application

Characteristics

A complete range of cable ties for control panel applications.

- Available in different packaging quantities to respond to the user's need
- Available in different lengths and tensile strengths
- Sophisticated, ergonomic fastening installation tools and easy to use cable ties dispenser

Technical Information

Material	Polyamide 6.6
Temperature range	-40°C to +85°C
Colour	UV-resistant black
Flammability rating	UL 94 V-2
Other properties	UV-resistant, Halogen free, Silicone free

GID-Ordering code	Product Ref.	Length	Width	Min. tensile strength	Bundle diameter from... to...	Quantity	Bags/ Carton
		L	W				
		[mm]	[mm]	[N]	[mm]	[pieces]	
7TCA300060R0000	SKT100-80X-100	100	2.5	80	1.5 - 22	100	550
7TCA300080R0000	SKT100-80X	100	2.5	80	1.5 - 22	1000	70
7TCA300060R0001	SKT140-80X-100	140	2.5	80	1.5 - 33	100	450
7TCA300080R0001	SKT140-80X	140	2.5	80	1.5 - 33	1000	55
7TCA300060R0002	SKT160-80X-100	160	2.5	80	1.5 - 40	100	400
7TCA300080R0002	SKT160-80X	160	2.5	80	1.5 - 40	1000	45
7TCA300060R0003	SKT200-80X-100	200	2.5	80	1.5 - 53	100	300
7TCA300080R0003	SKT200-80X	200	2.5	80	1.5 - 53	1000	32
7TCA300140R0000	SKT140-180X-100	140	3.6	180	2 - 33	100	300
7TCA300160R0000	SKT140-180X	140	3.6	180	2 - 33	1000	30
7TCA300140R0001	SKT200-180X-100	200	3.6	180	2 - 53	100	200
7TCA300160R0001	SKT200-180X	200	3.6	180	2 - 53	1000	22
7TCA300140R0002	SKT300-180X-100	300	3.6	180	2 - 76	100	120
7TCA300160R0002	SKT300-180X	300	3.6	180	2 - 76	1000	12
7TCA300140R0003	SKT370-180X-100	370	3.6	180	2 - 102	100	120
7TCA300160R0003	SKT370-180X	370	3.6	180	2 - 102	1000	12
7TCA300220R0000	SKT188-220X-100	188	4.8	220	3 - 46	100	160
7TCA300240R0000	SKT188-220X	188	4.8	220	3 - 46	1000	16
7TCA300220R0001	SKT215-220X-100	215	4.8	220	3 - 53	100	11
7TCA300240R0001	SKT215-220X	215	4.8	220	3 - 53	1000	13
7TCA300220R0002	SKT250-220X-100	250	4.8	220	3 - 60	100	120
7TCA300240R0002	SKT250-220X	250	4.8	220	3 - 60	1000	12
7TCA300220R0003	SKT300-220X-100	300	4.8	220	3 - 76	100	80
7TCA300240R0003	SKT300-220X	300	4.8	220	3 - 76	1000	8
7TCA300220R0004	SKT370-220X-100	370	4.8	220	3 - 102	100	70
7TCA300240R0004	SKT370-220X	370	4.8	220	3 - 102	1000	7
7TCA300300R0000	SKT300-540X-100	300	7.6	540	7 - 76	100	50
7TCA300320R0000	SKT300-540X	300	7.6	540	7 - 76	500	10
7TCA300300R0001	SKT370-540X-100	370	7.6	540	7 - 102	100	40
7TCA300320R0001	SKT370-540X	370	7.6	540	7 - 102	500	8
7TCA300300R0003	SKT450-540X-50	450	7.6	540	7 - 142	50	50
7TCA300300R0002	SKT750-540X-50	750	7.6	540	7 - 218	50	30
7TCA300360R0000	SKT776-780X-50	776	9.0	780	7 - 228	50	30
7TCA300360R0001	SKT912-780X-50	912	9.0	780	7 - 263	50	10

