



Number of Poles
2 & Main Breaker

Voltage Rating
120/240Vac

Current Rating
70A to 225A

Protection
Thermal Magnetic

Molded Case Circuit Breakers
Q-Line: Main Breaker 70A to 225A

Type
Thermal Magnetic: THQL, THHQL, THQMV

Operating Conditions: Curve represents cold trip with no prior load. Curves apply at 60 Hertz with reference ambient temperature of 40°C wired with conductors of corresponding rating. Refer to technical guide from the UL catalog for more information regarding thermal application.

Adjustments
Long-time delay thermal trip: not adjustable.
Instantaneous magnetic trip: not adjustable.