



EVA-DIP-22/DALI/ZWART

Self-contained 2 watt, black maintained recess 22 meter led luminaire, including DALI control module, series Evago, including the pictogram PP 220/51 RAL 9011

Product Information

Type	EVA-DIP-22/DALI/ZWART
Catalog number	4530216962
Category_	Escape route signalisation
GTIN	08713812770352
GID	7TCA091180R0359
Serie	Evago
Warranty (Year)	5
Other	Including round and square decorative covers. Including DALI communication module, conform EN62386



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Aluminium / plastic
Colour housing	Black
Material	Aluminium / polycarbonate
Colour	Black
Length (mm)	235
Width (mm)	84
Height/depth (mm)	134
Maximum outer diameter (mm)	84
Built-in length (mm)	300
Built-in width (mm)	68
Built-in diameter (mm)	68
Built-in depth (mm)	48
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiMH
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5000
CRI	80
Protection class	II
Degree of protection (IP)	40
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Single / double-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	22

Circuit	Other
Power consumption maintained mode (W)	4
Apparent power consumption maintained mode (VA)	4,4
Nominal current (mA)	19
Powerfactor	> 0,9
Temperature range (°C)	5 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30502
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,961
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	300 x 205 x 88