

STOCK LIST

Fastening solutions


Cable tie and wiring duct suggested stock list

Ty-Rap® | **Catamount**® | **Ty-Duct**®






Suggested stock list

Ty-Rap® high-performance cable ties

	ABB catalog no.	ABB UPC no.	Length	Color	Pack qty.	
Nylon 6.6 cable ties — Miniature 18 lb.						
	TY523M	78621080507	4"	Natural	100	
	TY523MX	78621080508	4"	UV black	100	
	TY23M	78621082436	4"	Natural	1000	
	TY23MX	78621082446	4"	UV black	1000	
	TY52315M	78621087544	7"	Natural	100	
	TY52315MX	78621087545	7"	UV black	100	
	TYB2315M	78621088355	7"	Natural	1000	
	TYB2315MX	78621088506	7"	UV black	1000	
	TY5232M	78621083077	8"	Natural	100	
	TY5232MX	78621083937	8"	UV black	100	
	TY232M	78621083069	8"	Natural	1000	
	TY232MX	78621088417	8"	UV black	1000	
	Nylon 6.6 cable ties — Intermediate 30–40 lb.					
		TY524M	78621080605	5.5"	Natural	100
TY524MX		78621080699	5.5"	UV black	100	
TY24M		78621082447	5.5"	Natural	1000	
TY24MX		78621082644	5.5"	UV black	1000	
TY5242M		78621083079	8"	Natural	100	
TY5242MX		78621086988	8"	UV black	100	
TY242M		78621083071	8"	Natural	1000	
TY242MX		78621087103	8"	UV black	1000	
TY526M		78621082549	11"	Natural	100	
TY526MX		78621083936	11"	UV black	100	
TY26M		78621082468	11"	Natural	1000	
TY26MX		78621083987	11"	UV black	1000	
Nylon 6.6 cable ties — Standard 50 lb.						
		TY525M	78621080509	7"	Natural	100
	TY525MX	78621080510	7"	UV black	100	
	TY25M	78621082457	7"	Natural	1000	
	TY25MX	78621082467	7"	UV black	1000	
	TY5253M	78621086989	11"	Natural	100	
	TY5253MX	78621088513	11"	UV black	100	
	TY253M	78621083990	11"	Natural	1000	
	TY253MX	78621071504	11"	UV black	1000	
	TY528M	78621080513	14"	Natural	100	
	TY528MX	78621080514	14"	UV black	100	
	TY28M	78621082479	14"	Natural	1000	
	TY28MX	78621082484	14"	UV black	1000	




Suggested stock list

Ty-Rap® high-performance cable ties

	ABB catalog no.	ABB UPC no.	Length	Color	Pack qty.
Nylon 6.6 cable ties — Heavy duty 120 lb.					
	TY527M	78621080511	13"	Natural	50
	TY527MX	78621080512	13"	UV black	50
	TY27M	78621082469	13"	Natural	500
	TY27MX	78621082478	13"	UV black	500
	TY5275M	78621087081	18"	Natural	50
	TY5275MX	78621087085	18"	UV black	50
	TY529M	78621083073	30"	Natural	50
	TY529MX	78621083890	30"	UV black	50
Nylon 6.6. adhesive mounting bases					
	TC344A	78621080495	¾" x ¾"	Natural	1000
	TC344AX	78621006876	¾" x ¾"	UV black	1000
	TC345A	78621086804	1" x 1"	Natural	1000
	TC345AX	78621006683	1" x 1"	UV black	1000
Cable tie installation tools — polymer					
	ERG50	78620986729	For 18–50 lb. ties	Orange	1
	ERG120	78620986730	For 50–120 lb. ties	Orange	1





Suggested stock list

Catamount® general application cable ties

	ABB catalog no.	ABB UPC no.	Length	Color	Pack qty.
Nylon 6.6 cable tie — Miniature 18 lb.					
	L-4-18-9-C	728494914602	4"	Natural	100
	L-4-18-0-C	728494914404	4"	UV black	100
	L-4-18-9-M	728494914701	4"	Natural	1000
	L-4-18-0-M	728494914503	4"	UV black	1000
	L-8-18-9-C	728494917801	8"	Natural	100
	L-8-18-0-C	728494917603	8"	UV black	100
	L-8-18-9-M	728494917900	8"	Natural	1000
	L-8-18-0-M	728494917702	8"	UV black	1000
Nylon 6.6 cable tie — Intermediate 30–40 lb.					
	L-5-30-9-C	728494915609	5"	Natural	100
	L-5-30-0-C	728494915401	5"	UV black	100
	L-5-30-9-M	728494915708	5"	Natural	1000
	L-5-30-0-M	728494915500	5"	UV black	1000
	L-8-40-9-C	728494918402	8"	Natural	100
	L-8-40-0-C	728494918204	8"	UV black	100
	L-8-40-9-M	728494918501	8"	Natural	1000
	L-8-40-0-M	728494918303	8"	UV black	1000
	L-11-40-9-C	728494933030	11"	Natural	100
	L-11-40-0-C	728494933016	11"	UV black	100
	L-11-40-9-D	728494933047	11"	Natural	500
	L-11-40-0-D	728494933023	11"	UV black	500
	L-14-40-9-C	728494933153	14"	Natural	100
	L-14-40-0-C	728494933139	14"	UV black	100
	L-14-40-9-D	728494933160	14"	Natural	500
	L-14-40-0-D	728494933146	14"	UV black	500
Nylon 6.6 cable tie — Standard 50 lb.					
	L-7-50-9-C	728494917207	7"	Natural	100
	L-7-50-0-C	728494917009	7"	UV black	100
	L-7-50-9-M	728494917306	7"	Natural	1000
	L-7-50-0-M	728494917108	7"	UV black	1000
	L-11-50-9-C	728494911205	11"	Natural	100
	L-11-50-0-C	728494911007	11"	UV black	100
	L-11-50-9-D	728494911304	11"	Natural	500
	L-11-50-0-D	728494911106	11"	UV black	500
	L-14-50-9-C	728494912608	14"	Natural	100
	L-14-50-0-C	728494912400	14"	UV black	100
	L-14-50-9-D	728494912707	14"	Natural	500
	L-14-50-0-D	728494912509	14"	UV black	500

Suggested stock list

Catamount® general application cable ties

	ABB catalog no.	ABB UPC no.	Length	Color	Pack qty.
Nylon 6.6 cable tie — Heavy duty 120 lb.					
	L-14-120-9-L	786210080284	14"	Natural	50
	L-14-120-0-L	786210080307	14"	UV black	50
	L-14-120-9-C	728494911700	14"	Natural	100
	L-14-120-0-C	728494911601	14"	UV black	100
	L-18-120-9-L	728494912714	18"	Natural	50
	L-18-120-0-L	728494912738	18"	UV black	50
	L-24-120-9-L	728494912745	24"	Natural	50
	L-24-120-0-L	728494912769	24"	UV black	50
	L-28-120-9-L	728494125855	28"	Natural	50
	L-28-120-0-L	728494125763	28"	UV black	50
Nylon 6.6 cable tie — Super heavy duty 175 lb.					
	L-24-175-9-L	728494912905	24"	Natural	50
	L-24-175-0-L	728494912806	24"	UV black	50
	L-36-175-9-L	728494071558	36"	Natural	50
	L-36-175-0-L	728494105581	36"	UV black	50
	L-48-175-9-L	728494913902	48"	Natural	50
	L-48-175-0-L	728494913605	48"	UV black	50
	L-28-250-0-L	728494138015	28"	UV black	50
	Nylon 6.6. adhesive mounting base				
	MPNY-750-9-C	728494081526	¾" x ¾"	Natural	100
	MPNY-750-0-C	728494095356	¾" x ¾"	UV black	100
	MPNY-1000-9-C	728494110400	1 x 1	Natural	100
	MPNY-1000-0-C	728494100999	1 x 1	UV black	100
Cable tie installation tools — polymer					
	ERG50	78620986729	For 18–50 lb. ties	Orange	1
	ERG120	78620986730	For 50–120 lb. ties	Orange	1
	L-400-C	72849406807	For 18–50 lb. ties	Blue	1
	WT1-TB	78621088011	For 18–50 lb. ties	Orange	1
	WT2-TB	78621088451	For 50–120 lb. ties	Black	1

Suggested stock list

Ty-Duct® wiring duct and covers



Width (in.)	Height (in.)	Narrow slot	Wide slot	Solid wall	Round hole	Covers
		ABB catalog no.	ABB catalog no.	ABB catalog no.	ABB catalog no.	ABB catalog no.
0.5	0.5	-	-	-	-	-
0.5	1	-	-	-	-	-
0.75	0.75	-	-	-	-	TYD75CPG6
0.75	1	-	TYD75X1WPG6	TYD75X1SPG6	-	-
0.75	1.5	TYD75X15NPG6	TYD75X15WPG6	TYD75X15SPG6	-	-
0.75	2	-	TYD75X2WPG6	TYD75X2SPG6	-	-
1	1	TYD1X1NPG6	TYD1X1WPG6	TYD1X1SPG6	-	TYD1CPG6
1	1.5	TYD1X15NPG6	TYD1X15WPG6	TYD1X15SPG6	TYD1X15RPG6	-
1	2	TYD1X2NPG6	TYD1X2WPG6	TYD1X2SPG6	TYD1X2RPG6	-
1	3	TYD1X3NPG6	TYD1X3WPG6	TYD1X3SPG6	TYD1X3RPG6	-
1	4	TYD1X4NPG6	TYD1X4WPG6	TYD1X4SPG6	TYD1X4RPG6	-
1.5	1	TYD15X1NPG6	TYD15X1WPG6	TYD15X1SPG6	-	TYD15CPG6
1.5	1.5	TYD15X15NPG6	TYD15X15WPG6	TYD15X15SPG6	TYD15X15RPG6	-
1.5	2	TYD15X2NPG6	TYD15X2WPG6	TYD15X2SPG6	TYD15X2RPG6	-
1.5	3	TYD15X3NPG6	TYD15X3WPG6	TYD15X3SPG6	TYD15X3RPG6	-
1.5	4	TYD15X4NPG6	TYD15X4WPG6	TYD15X4SPG6	TYD15X4RPG6	-
2	1	TYD2X1NPG6	TYD2X1WPG6	TYD2X1SPG6	-	TYD2CPG6
2	1.5	TYD2X15NPG6	TYD2X15WPG6	TYD2X15SPG6	TYD2X15RPG6	-
2	2	TYD2X2NPG6	TYD2X2WPG6	TYD2X2SPG6	TYD2X2RPG6	-
2	3	TYD2X3NPG6	TYD2X3WPG6	TYD2X3SPG6	TYD2X3RPG6	-
2	4	TYD2X4NPG6	TYD2X4WPG6	TYD2X4SPG6	TYD2X4RPG6	-
2	5	TYD2X5NPG6	TYD2X5WPG6	TYD2X5SPG6	-	-
2.5	2	TYD25X2NPG6	TYD25X2WPG6	TYD25X2SPG6	-	TYD25CPG6
2.5	3	TYD25X3NPG6	TYD25X3WPG6	TYD25X3SPG6	-	-
2.5	4	TYD25X4NPG6	TYD25X4WPG6	TYD25X4SPG6	-	-
3	1	TYD3X1NPG6	TYD3X1WPG6	TYD3X1SPG6	TYD3X1RPG6	TYD3CPG6
3	2	TYD3X2NPG6	TYD3X2WPG6	TYD3X2SPG6	TYD3X2RPG6	-
3	3	TYD3X3NPG6	TYD3X3WPG6	TYD3X3SPG6	TYD3X3RPG6	-
3	4	TYD3X4NPG6	TYD3X4WPG6	TYD3X4SPG6	TYD3X4RPG6	-
3	5	TYD3X5NPG6	TYD3X5WPG6	TYD3X5SPG6	-	-
4	1.5	-	TYD4X15WPG6	TYD4X15SPG6	TYD4X15RPG6	TYD4CPG6
4	2	TYD4X2NPG6	TYD4X2WPG6	TYD4X2SPG6	TYD4X2RPG6	-
4	3	TYD4X3NPG6	TYD4X3WPG6	TYD4X3SPG6	TYD4X3RPG6	-
4	4	TYD4X4NPG6	TYD4X4WPG6	TYD4X4SPG6	TYD4X4RPG6	-
4	5	TYD4X5NPG6	TYD4X5WPG6	TYD4X5SPG6	-	-
6	4	-	-	-	-	TYD6CPG6

Notes:

PVC duct is UL® Recognized , CSA Certified and CE Compliant.

Ty-Duct color code: G = gray, W = white, B = black, I = intrinsic blue

Suggested stock list

Ty-Duct® tools




	Tools	Material	Coating	ABB catalog no.
	Handheld duct cutter	Stainless steel	Orange	SX25-TB
	Wiring duct finger cutter	Stainless steel	Orange	DK-65TB
	Wiring duct bench-mount cutting tool	Stainless steel	Metallic	DC-125TB



ABB Installation Products Inc.

Electrification Business
860 Ridge Lake Blvd.
Memphis, TN 38120

electrification.us.abb.com

ABB has made every attempt to ensure the accuracy and reliability of the contents of this document. However, all content is provided for general informational purposes only, and ABB makes no guaranty or warranty, express or implied, as to the accuracy of any technical content, or that the information contained in this publication will be error free and all such guarantees or warranties are expressly disclaimed. ABB may change or modify

the contents at any time, without prior notice. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction or utilization of its contents — in whole or in parts — is forbidden without prior written consent of ABB.
© 2023 ABB Installation Products Inc.
and/or its affiliated companies.
All rights reserved.