

PRODUCT SPECIFICATION

IND1LS5

Indulux 230v AC IP68 Surface

Catalogue Number **IND1LS5**
 GID **7TCA091720R0175**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Mains / Slave Operation**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **316L stainless steel/plastic**
 Colour **Silver/Clear**
 Dimensions (LxWxD) **398 x 100 x 100 mm**
 Temperature Range **-25 to +40°C**
 Weight **1.4 Kg**

Emergency Duration (Hours) **Mains / Central Battery Hours**
 Battery **Mains / Central Battery**
 Monitoring Equipment **None**
 Lamp **1 x 5W LED**
 Emergency Light Output (Lumens) **400**
 Average Lifespan light source (Hours) **60000 Hours**
 Light Colour/Temperature/CRI **White / 6000 / 80**
 Degree of Protection **IP68 IK10**

Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **17**
 Nominal Voltage **220-240v AC/DC 0-60Hz**
 Power Consumption **7 VA / 6.5 Watts**
 Current **Nominal: 30mA (mA) Inrush: 2A**

Accessories

102601K Cable Entry Cover kit
102702K



Configurable pictograms included



Luminaire

