

## Product Specification

### Indulux



Luminaire

#### IND1LS5DS

#### Indulux LED D/S 230V Slave

Catalogue Number	IND1LS5DS
Category	Combined Escape route or Sign Luminaire
GTIN	05415022466744
GID	7TCA091720R0176
Warranty (Year)	3
Other	Refer to ABB warranty terms & conditions



Configurable pictograms included

Power Supply System	Mains / Slave Operation
Mounting Method	Ceiling, Wall
Mounting Form	Surface
Material Housing	316L stainless steel/plastic
Colour Housing	White/Grey
Material Cover	No cover supplied
Material	316L stainless steel/plastic
Colour	Silver/Clear
Length (mm)	398
Width (mm)	100
Height/depth (mm)	100
Nominal Voltage (V)	220-240
Voltage Type	AC/DC 0-60Hz
Duration (hours)	Mains / Central Battery
Battery	Mains / Central Battery
Monitoring Equipment	None
Lamp Type	LED
Lamp Power	10
Number of Lamps	2
Light output in Emergency Operation (lm)	800
Average Lifespan light source (hours)	60000
Colour of Light	White
Colour Temperature (K)	6000
CRI	80
Degree of Protection (IP)	68
Impact Strength (IK)	10
Wiring System	Mains / CBU
Type of Legend	Varies

Legend style	Internal Foil supplied
Recognition distance (m)	17
Power Consumption Maintained mode (W)	13
Power Consumption Maintained mode (VA)	14
Nominal current (mA)	60
Inrush Current (A to 0.1ms)	2
Power Factor	0.92
Temperature range (°C)	-25 to +40°C
Weight (Kg)	1.4
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	430 x 130 x 140

### Accessories

**102601K** Cable Entry Cover kit

**102702K** Battery replacement