

PRODUCT SPECIFICATION

IR2WWA3LS1X

Weatherforce Self-Contained 27M IP65 IR2 Surface

Catalogue Number **IR2WWA3LS1X**
GID **7TCA091170R0038**
Warranty **3 Year/s Refer to ABB warranty terms & conditions**
Power Supply System **Self-Contained (individual battery)**
Mounting Method/Form **Ceiling, Wall Surface**
Housing Material **Metal**
Colour **White**
Dimensions (LxWxD) **400 x 140 x 58 mm**
Temperature Range **0 to 30°C**
Weight **1.49 Kg**

Emergency Duration (Hours) **3 Hours**
Battery **NiCd**
Monitoring Equipment **IR2 test**
Lamp **1 x 2W LED**
Emergency Light Output (Lumens) **207**
Average Lifespan light source (Hours) **100000 Hours**
Light Colour/Temperature/CRI **White / 4000 / 80**
Degree of Protection **IP65 IK10**

Type of Legend **Single or Double Sided**
Exit Sign Viewing/Recognition Distance (m) **27**
Nominal Voltage **220-240v AC 50/60Hz**
Power Consumption **6.1 VA / 3.9 Watts**
Current **Nominal: 25.5mA (mA) Inrush: 0.7A**

Accessories

XEN2/2DV32 Double sided Diffuser with Down+Down ISO7010 Legend
XEN3/6DV32 Double sided Diffuser with Left+Right ISO7010 Legend
XEN5/5DV32 Double sided Diffuser with Up+Up ISO7010 Legend

XB10DV32 Double sided Diffuser with Blank+Arabic English Legend
XB11DV32 Double sided Diffuser with Arabic English+Arabic English Legend
XB23DV32 Double sided Diffuser with Arabic English Left+Arabic English Right Legend
XB50DV32 Double sided Diffuser with Blank+Arabic English Up Legend
XB66DV32 Double sided Diffuser with Arabic English Down+Arabic English Down Legend

BBZ Semi recessing bezel White



Double Sided Exit Sign
IR2WWA3LS1X + XEN2/2DV32

