



## EVA-R-CLI/FLX

Slave 2 watt, 230 Volt round white recess led luminaire, including control module, series Evago. Light distribution: long (L), for example hallways

### Product Information

Type	EVA-R-CLI/FLX
Catalog number	5520257361
Category_	Escape route lighting
GTIN	08713812762142
GID	7TCA091140R0368
Serie	Evago
Warranty (Year)	5



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling
Mounting form	Recess
Material housing	Aluminium / plastic
Colour housing	White
Material	Aluminium / polycarbonate
Colour	White
Length (mm)	226
Width (mm)	100
Height/depth (mm)	38
Maximum outer diameter (mm)	100
Built-in length (mm)	226
Built-in width (mm)	68
Built-in diameter (mm)	68
Built-in depth (mm)	35
Nominal voltage (V)	230
Voltage type	DC
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	203
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	42
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	5
Apparent power consumption maintained mode (VA)	5,5
Nominal current (mA)	24
Powerfactor	0,9

Temperature range (°C) 0 ~ +40

**Article Details**

Product class Emergency luminaire  
E-code EC001957  
Discount group 30406  
Harmonized code 9405408440  
GLN 8713812000008

**Ordering information**

Orderable Yes  
Order-Unit Pieces  
Minimum order quantity 1  
Order Increment 1

**Supply Information**

Weight (kg) 0,320  
Packaging Cardboard box  
Packaging dimensions (LxWxH) (mm) 225 x 170 x 62