

Product Specification

Indulux



Luminaire

CTIND3LS5

Indulux LED S/S M3 CT

Catalogue Number	CTIND3LS5
Category	Combined Escape route or Sign Luminaire
GTIN	05415022466966
GID	7TCA091720R0181
Warranty (Year)	3
Other	Refer to ABB warranty terms & conditions



Configurable pictograms included

Power Supply System	Self-Contained (individual battery)
Mounting Method	Ceiling, Wall
Mounting Form	Surface
Material Housing	316L stainless steel/plastic
Colour Housing	White/Grey
Material Cover	No cover supplied
Material	316L stainless steel/plastic
Colour	Silver/Clear
Length (mm)	398
Width (mm)	100
Height/depth (mm)	100
Nominal Voltage (V)	220-240
Voltage Type	AC 50Hz
Duration (hours)	3
Battery	NiMH
Monitoring Equipment	Naveo test
Lamp Type	LED
Lamp Power	5
Number of Lamps	1
Light output in Emergency Operation (lm)	200
Average Lifespan light source (hours)	60000
Colour of Light	White
Colour Temperature (K)	6000
CRI	80
Degree of Protection (IP)	68
Impact Strength (IK)	10
Wiring System	Maintained / non-maintained circuit
Type of Legend	Varies

Legend style	Internal Foil supplied
Recognition distance (m)	17
Power Consumption Maintained mode (W)	3.5
Power Consumption Maintained mode (VA)	7.5
Nominal current (mA)	32.5
Inrush Current (A to 0.1ms)	
Power Factor	0.48
Temperature range (°C)	0 to 40°C
Weight (Kg)	1.6
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	430 x 130 x 140

Accessories

102601K Cable Entry Cover kit

102702K Battery replacement