

PRODUCT SPECIFICATION

# CTEG3LS1-S32

## Guideway Self-Contained 32M IP40 Naveo Surface/Wall

Catalogue Number **CTEG3LS1-S32**  
 GID **7TCA091180R0257**  
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**  
 Power Supply System **Self-Contained (individual battery)**  
 Mounting Method/Form **Ceiling, Wall Surface**  
 Housing Material **Aluminium/Plastic**  
 Colour **Silver**  
 Dimensions (LxWxD) **335 x 52 x 222 mm**  
 Temperature Range **5 to 35°C**  
 Weight **1.6 Kg**

Emergency Duration (Hours) **3**  
 Battery **NiMH**  
 Monitoring Equipment **Naveo®Pro**  
 Lamp **1 x 4W LED**  
 Emergency Light Output (Lumens) **Not Applicable**  
 Average Lifespan light source (Hours) **100000 Hours**  
 Light Colour/Temperature/CRI **White / 5000 / 80**  
 Degree of Protection **IP40**

Type of Legend **Single or Double Sided**  
 Exit Sign Viewing/Recognition Distance (m) **32**  
 Nominal Voltage **220-240v AC 50Hz**  
 Power Consumption **7.1 VA / 6.5 Watts**  
 Current **Nominal: 31mA (mA)**

### Accessories

- XEN2EG32** Down ISO7010 Legend Single Sided
- XEN3EG32** Left ISO7010 Legend Single Sided
- XEN6EG32** Right ISO7010 Legend Single Sided
- XEN5EG32** Up ISO7010 Legend Single Sided
- XBN1EG32** Arabic English Legend Single Sided
- XEN0G22** Blank Legend Single Sided

**EG-T4EG** Cover Discs (2x semi-circular, 2x rectangular) for Slave

- EG-TKIT50** Suspension Kit Pendant 50mm
- EG-TKIT100** Suspension Kit Pendant 100mm
- EG-WKIT150** Wire Suspension Kit 150mm

- XEN602EG32** Down ISO7010 Legend Flag Mount
- XEN603EG32** Left ISO7010 Legend Flag Mount
- XEN606EG32** Right ISO7010 Legend Flag Mount
- XEN605EG32** Up ISO7010 Legend Flag Mount



Exit Sign Flag Mount  
CTEG3LS1-S32 + XEN606EG32



Exit Sign Suspended  
CTEG3LS1-S32 + EG-TKIT50



Exit Sign Surface  
CTEG3LS1-S32

