

PRODUCT SPECIFICATION

DAEG3LS1-S22

Guideway Self-Contained 22M IP40 DALI Test Surface/Wall

Catalogue Number **DAEG3LS1-S22**
 GID **7TCA091180R0338**
 Warranty **4 Year/s Refer to ABB warranty terms & conditions**
 Power Supply System **Self-Contained (individual battery)**
 Mounting Method/Form **Ceiling, Wall Surface**
 Housing Material **Aluminium/Plastic**
 Colour **Silver**
 Dimensions (LxWxD) **235 x 66 x 172 mm**
 Temperature Range **5 to 35°C**
 Weight **1.5 Kg**

Nominal Voltage **220-240v AC 50Hz**
 Emergency Duration (Hours) **3 Hours**
 Battery **NiMH**
 Monitoring Equipment **DALI test**
 Lamp **1 x 2W LED**
 Light output in Emergency Operation **Not Applicable Lumens**
 Average Lifespan light source (hours) **100000 Hours**
 Light Colour/Temperature/CRI **White / 5000 / 80**
 Degree of Protection **IP 40 IK tbc**

Wiring System **Maintained / non-maintained circuit**
 Type of Legend **Single or Double Sided**
 Exit Sign Viewing/Recognition Distance (m) **22**
 Power Consumption **4.4 VA / 4 Watts**
 Nominal Current **19 (mA)**
 Inrush Current **tbc A to 0.1 ms**

Accessories

- XEN2EG22** Down ISO7010 Legend Single Sided
- XEN3EG22** Left ISO7010 Legend Single Sided
- XEN6EG22** Right ISO7010 Legend Single Sided
- XEN5EG22** Up ISO7010 Legend Single Sided
- XBN1EG22** Arabic English Legend Single Sided
- XEN0G22** Blank Legend Single Sided

EG-T4EG Cover Discs (2x semi-circular, 2x rectangular) for Slave

- EG-TKIT50** Suspension Kit Pendant 50mm
- EG-TKIT100** Suspension Kit Pendant 100mm
- EG-WKIT150** Wire Suspension Kit 150mm

- XEN602EG22** Down ISO7010 Legend Flag Mount
- XEN603EG22** Left ISO7010 Legend Flag Mount
- XEN606EG22** Right ISO7010 Legend Flag Mount
- XEN605EG22** Up ISO7010 Legend Flag Mount



Exit Sign Flag Mount
DAEG3LS1-S22 + XEN606EG22



Exit Sign Suspended
DAEG3LS1-S22 + EG-TKIT50



Exit Sign Surface
DAEG3LS1-S22

