



EVA-DSO/CIS/ALU

Self-contained 2 watt, aluminium maintained wall mount led luminaire, including control module, series Evago. Light distribution: spot (S), for example staircases

Product Information

Type	EVA-DSO/CIS/ALU
Catalog number	5513217157
Category_	Escape route lighting
GTIN	08713812766058
GID	7TCA091180R0267
Serie	Evago
Warranty (Year)	5



Characteristics

Power supply system	Self-contained individual battery
Continuous operation	Yes
Mounting Method	Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	Aluminium
Material	Aluminium / polycarbonate
Colour	Aluminium
Length (mm)	150
Width (mm)	150
Height/depth (mm)	35
Nominal voltage (V)	230
Voltage type	AC
Duration (hours)	1
Battery	NiMH
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	2
Number of lamps	1
Light output in emergency operation (lm)	176
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	5600
CRI	70
Protection class	II
Degree of protection (IP)	54
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Not applicable
Circuit	Other
Power consumption maintained mode (W)	3 / 2
Apparent power consumption maintained mode (VA)	3,5 / 2,85
Nominal current (mA)	15
Powerfactor	0,85 / 0,7
Temperature range (°C)	5 ~ +35

Article Details

Product class	Emergency luminaire
E-code	EC001957
Discount group	30502
Harmonized code	9405408440
GLN	8713812000008

Ordering information

Orderable	Yes
Order-Unit	Pieces
Minimum order quantity	1
Order Increment	1

Supply Information

Weight (kg)	0,969
Packaging	Cardboard box
Packaging dimensions (LxWxH) (mm)	225 x 170 x 62